

Product data sheet

Specifications



OptiLine 50 - movement detector - 2300 W - dark grey

INS66707

⚠ Discontinued on: Jun 30, 2022

⚠ Discontinued

Main

Range Of Product	OptiLine 50
Product Type	Movement detector
Sensor Type	PIR
Load Type	Fluorescent lamp with conventional ballast 2000 VA cos phi 0.9 Incandescent lamp 2300 W 230 V halogen lamp 2000 W Low voltage halogen lamp with ferromagnetic transformer 1050 W Dimmable fluocompact lamp 500 VA Ventilator 200 VA Heater 2300 W Contactor 200 VA Low voltage halogen lamp with electronic transformer 1150 W
Colour	Dark grey
Quantity Package 1 / Unit	1 piece

Complementary

Rated Power In W	2300 W
Rating	16 A at 250 V
Product Material	PC/ABS
Fixing Mode	Snap-fitted
Height	57 mm
Width	100 mm
Depth	50 mm

Environment

Operating Temperature	-5...35 °C
-----------------------	------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	5.7 cm
Package 1 Length	10 cm
Package 1 Weight	140 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations