

# Product data sheet

Specifications

## OptiLine 70 - ceiling frame - 1-sided pole - polar white



ISM20550P

 **Discontinued on:** Sep 30, 2022

 **Discontinued**

### Main

|                             |               |
|-----------------------------|---------------|
| Cabling Installation System | Pole          |
| Product Or Component Type   | Ceiling frame |

### Complementary

|                          |                           |
|--------------------------|---------------------------|
| Type Of Pole             | One-sided                 |
| Colour Tint              | Polar white (RAL 9003)    |
| Quantity Per Set         | Set of 1                  |
| Product Compatibility    | Unica wiring device       |
| Pole/Post Surface Finish | Anodized<br>Powder coated |
| Pole Fixing Mode         | Tension-mounted           |
| Fixing Mode              | Self-sticking             |
| Material                 | PS (polystyrene)          |
| Length                   | 170 mm                    |
| Height                   | 1 mm                      |
| Width                    | 111 mm                    |

### Environment

|                                       |             |
|---------------------------------------|-------------|
| Ambient Air Temperature For Operation | -25...60 °C |
| Ip Degree Of Protection               | IP40        |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 0.1 cm  |
| Package 1 Width              | 11.1 cm |
| Package 1 Length             | 17.0 cm |
| Package 1 Weight             | 13.0 g  |
| Unit Type Of Package 2       | BAG     |
| Number Of Units In Package 2 | 1       |
| Package 2 Height             | 0.1 cm  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |         |
|------------------------------|---------|
| Package 2 Width              | 15.0 cm |
| Package 2 Length             | 20.0 cm |
| Package 2 Weight             | 13.0 g  |
| Unit Type Of Package 3       | S02     |
| Number Of Units In Package 3 | 100     |
| Package 3 Height             | 15.0 cm |
| Package 3 Width              | 30.0 cm |
| Package 3 Length             | 40.0 cm |
| Package 3 Weight             | 1.6 kg  |

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

|                          |   |
|--------------------------|---|
| <b>Eu Rohs Directive</b> | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
|--------------------------|---|

|                              |   |
|------------------------------|---|
| <b>China Rohs Regulation</b> | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
|------------------------------|---|