

# Product data sheet

Specifications



## MGE Galaxy 3500 Parallel Maintenance Bypass, up to 3 units 20-30kVA 208V Floormount

G35TSBPAR20K30F

! Discontinued

! Discontinued on: Jul 5, 2021

! End-of-service on: Oct 18, 2023

### Overview

Lead Time Usually Ships within 2 Weeks

### Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
Rated Power In Va	90000 VA
Provided Equipment	Installation guide

### Physical

Height	148.7 cm
Width	35.1 cm
Depth	83.7 cm
Net Weight	144.09 kg
Mounting Support	Floor
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

### Input

Network Frequency	60 Hz
-------------------	-------

### Conformance

Standards	CSA C22.2 No 107.1 UL 1778
Product Certifications	CSA

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	0...45 °C
Storage Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage Altitude	0.00...9144.00 m
------------------	------------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	166.37 cm
Package 1 Width	110.49 cm
Package 1 Length	72.39 cm
Package 1 Weight	205 kg

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope

---