

Product data sheet

Specifications



MGE Galaxy 3500 Input Transformer MCCB 208/208 10-30kVA Floormount

G35TSBPXFM10K30F

! Discontinued

! Discontinued on: Nov 22, 2021

! End-of-service on: Oct 18, 2023

Overview

Presentation	Bypass cabinet with 208/208 integrated input transformer
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
Rated Power In Va	30000 VA
Provided Equipment	Installation guide

Physical

Height	148.7 cm
Width	35.1 cm
Depth	83.7 cm
Net Weight	330.91 kg
Mounting Support	Floor
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Network Frequency	60 Hz
-------------------	-------

Conformance

Standards	CSA C22.2 No 107.1 UL 1778
Product Certifications	CSA

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	0...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	166.37 cm
Package 1 Width	110.49 cm
Package 1 Length	72.39 cm
Package 1 Weight	365 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
