


Product data sheet

Specifications



MGE Galaxy 3500 Extended Run Frame with 2 Battery Modules Exp. to 6

G35TXR2B6

⚠ Discontinued on: Jul 5, 2021

⚠ End-of-service on: Oct 18, 2023

⚠ Discontinued

Overview

Lead Time Usually Ships within 2 Weeks

Main

Main Input Voltage 208 V 3 phases
400 V 3 phases

Battery Type Lead-acid battery

Provided Equipment Installation guide
User manual

Batteries & Runtime

Battery Location External frame

Number Of Battery Free Slots 0

Number Of Battery Filled Slots 2

Device Mounting Enclosed battery cabinet

Physical

Height 149.9 cm

Width 52.3 cm

Depth 92.5 cm

Net Weight 388 kg

Mounting Mode Not rack-mountable

Input

Network Frequency 50/60 Hz

Conformance

Standards CSA C22.2 No 107.1

Product Certifications CSA

Environmental

Ambient Air Temperature For Operation 0...40 °C

Ambient Air Temperature For Storage 0...30 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	164.3 cm
Package 1 Width	106.2 cm
Package 1 Length	65 cm
Package 1 Weight	418 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
