

# Product data sheet

Specifications



## MGE Galaxy 300 15kVA 400V 3:1 with 10min Battery, Start-up 5x8

G3HT15K3IB1S

⚠ Discontinued on: Apr 29, 2024

⚠ To be end-of-service on: Dec 31, 2029

⚠ Discontinued - Service only

### Overview

Presentation	Effective three phase power protection against downtime and data loss for mission critical applications. Ruggedized version including dust filter and conformance coated boards for harsh environments.
Lead Time	Usually Ships within 2 Weeks

### Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	12000 W
Rated Power In Va	15000 VA
Output Connector Type	Hard wire 3-wire (H N + E) 1
Battery Type	Lead-acid battery
Provided Equipment	CD with software Installation guide Network management card Start-up service User manual

### Batteries & Runtime

Efficiency	<a href="#">View Efficiency Graph</a>
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage
Battery Power In Vah	0 VAh runtime
Extended Runtime	0

### General

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

## Physical

Height	130 cm
Width	40 cm
Depth	95 cm
Net Weight	233 kg
Mounting Preference	No preference
Usb Compatible	No

## Input

Network Frequency	45...65 Hz
Number Of Input Connectors	1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	323...437 V adjustable 380 V 340...460 V adjustable 400 V 357...477 V adjustable 415 V 340...477 V
Maximum Input Current	24 A
Switching Current Capacity	63 A
Input Harmonic Distortion	Less than 5 % for full load
Input Protection Type	GL fuse
Inrush Current	200 A peak
Load Power Factor	0.5 leading to 0.5 lagging
Input Power Factor At Full Load	0.97

## Output

Maximum Configurable Power In W	12000 W
Harmonic Distortion	Less than 5 %
Output Frequency	50/60 Hz +/- 5 % sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest Factor	2.5 : 1
Wave Type	Sine wave
Output Voltage Tolerance	+/- 2% static and 100% load step
Output Harmonic Distortion	< 3% linear load and < 5% non-linear load
Output Overload Operation	60 seconds at 120% and 30 seconds at 145%
Required Output Current Protection	125 A
Maximum Output Current	98 A
Maximum Configurable Power In Va	15000 VA

## Conformance

Product Certifications	CE TÜV
Standards	EN/IEC 62040-1-1 EN/IEC 62040-2 EN/IEC 62040-3 IEC 61000-4-5 IEC 62040-2 VFI-SS-111

## Environmental

Ambient Air Temperature For Operation	0...35 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-10...60 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m
Acoustic Level	54.5 dBA
Heat Dissipation	1045 Btu/h
Ip Degree Of Protection	IP20

## Communications & Management

Preinstalled Device	Network management card
Control Panel	Multifunction LCD status and control console
Emergency Power Off	Yes

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	143.993 cm
Package 1 Width	80.01 cm
Package 1 Length	96.495 cm
Package 1 Weight	257.459 kg

## Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency

## Resource performance

✓ Energy Efficient Product

---

✓ Take-Back Program Available

---

## Well-being performance

✓ Mercury Free

---

Eu Rohs Directive

Not compliant

---

Environmental Disclosure

[Product Environmental Profile](#)

---

Circularity Profile

[End of Life Information](#)

---