

Product data sheet

Specifications



Switch disconnecter fuse, TeSys GS, 3P, 30A, fuse type UL, fuse size CC

GS1DDU3

Main

| | |
|---|--------------------------|
| Range | TeSys |
| Product Name | TeSys GS |
| Device Short Name | GS1 DD |
| Product Or Component Type | Switch-disconnector-fuse |
| Device Application | Protection |
| Design | Compact |
| Poles Description | 3P |
| Protected Poles Description | 3t |
| Contacts Type And Composition | 3 NO |
| [Ith] Conventional Free Air Thermal Current | 30 A (at 40 °C) |
| [Ie] Rated Operational Current | 30 A |
| Fuse Type | UL |
| Fuse Size | CC |
| Network Type | AC DC |
| Network Frequency | 50/60 Hz |

Complementary

| | |
|--|--|
| Type Of Operating Handle | External frontal Direct frontal |
| Mounting Support | Rail Plate |
| [UI] Rated Insulation Voltage | 690 V |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |
| Rated Operational Power In W | 15 kW at 400 V 18.5 kW at 500 V 25 kW at 690 V |
| Short-Circuit Withstand | 5.5 kA |
| Mechanical Durability | 10000 cycles |
| Electrical Durability | 6000 cycles |
| Connections - Terminals | Power circuit: lugs-ring terminals2...6 mm² |
| Tightening Torque | Power circuit: 3 N.m |

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|--|
| Standards | UL 489 CSA C22.2 No 5 |
| Product Certifications | LROS (Lloyds register of shipping) LOVAG ASEFA |
| Ip Degree Of Protection | IP20 conforming to IEC 60529 (with terminal cover) |
| Ambient Air Temperature For Operation | -20...70 °C |
| Ambient Air Temperature For Storage | -40...80 °C |
| Fire Resistance | 960 °C body conforming to IEC 60695-2-1 |
| Height | 116 mm |
| Width | 97 mm |
| Depth | 83.5 mm |
| Net Weight | 0.6 kg |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 12.400 cm |
| Package 1 Width | 14.400 cm |
| Package 1 Length | 18.000 cm |
| Package 1 Weight | 550.000 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 8 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 4.875 kg |
| Unit Type Of Package 3 | P06 |
| Number Of Units In Package 3 | 64 |
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 54.204 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|---------------------------|--|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |