

Product data sheet

Specifications



Fuse connection unit, Vivace, 13A, 250V, white

KB30FSG

Main

Range	Vivace
Device Short Name	KB30
Product Or Component Type	Fuse connection unit
Device Application	Power supply
Device Presentation	Complete mechanism
Main Colour Tint	White
Colour Tint	Wall: white

Complementary

Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Surface Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	35 mm
Rated Current	13 A at 250 V AC, resistive
Network Frequency	50 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	L in L out N in N out Earth
Tightening Torque	0.4 N.m
Clamping Connection Capacity	2 x 4 mm ² power circuit 3 x 2.5 mm ² incoming 1 x 1.5 mm ² outgoing 1 x 2.5 mm ² input
Width	87 mm
Height	87 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	35 mm
-------	-------

Environment

Standards	BS 1363-4
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	0...60 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.5 cm
Package 1 Length	14.6 cm
Package 1 Weight	116.9 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.239 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	11940 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)