


Product data sheet

Specifications



16AX 250V 2 Gang 1 Way Switch

KB32_1

Main

Range	Vivace
Product or component type	Switch
Device short name	KB32
Device application	Control
Switch function	1-way

Complementary

Device presentation	Complete mechanism
Actuator	Rocker
Number of gangs	2 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	16 AX at 250 V AC, inductive 16 AX at 250 V AC, fluorescent
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	pillar terminal
Terminal identifier	L2 COM L1
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm ²
Width	87 mm

Height	87 mm
--------	-------

Environment

Standards	IEC 60669-1 MS IEC 60669-1 SS 227
-----------	---

Ambient air temperature for operation	-5...40 °C
---------------------------------------	------------

Relative humidity	0...95 %
-------------------	----------

Environmental characteristic	Indoor use
------------------------------	------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Weight	93.75 g
------------------	---------

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)