

Product data sheet

Specifications



Galaxy VS UPS 40kW 400V, 2 internal 9Ah smart modular battery strings, expandable to 4, Start-up 5x8

GVSUPS40KB4HS

Overview

Presentation	Highly efficient, easy-to-deploy 40kW, 400V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. Includes 5x8 start-up service and 2 smart high-capacity modular battery strings, expandable to 4 strings for extended runtime. Runtime charts available in the Documents tab.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated Power In W	40 kW
Rated Power In Va	40 kVA
Output Connector Type	Hard wire 5-wire (3P + N + E) 1
Battery Type	Internal modular battery VRLA
Provided Equipment	Battery modules ship installed Dust filter EcoStruxure IT ready (UPS) Installation guide Integrated network management Power modules ship installed Start-up service

Batteries & Runtime

Efficiency	View Efficiency Graph
Battery Voltage	480 V
Discharge Battery Voltage	384 V DC
Max Current Discharge	81 A
Battery Power In Vah	0 VAh runtime
Extended Runtime	0

General

Bypass Voltage Tolerance	+/- 10 %
Redundant	No

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Or Component Type	Uninterruptible power supply (UPS)
---------------------------	------------------------------------

Physical

Colour	White
Height	148.5 cm
Width	52.1 cm
Depth	84.7 cm
Net Weight	460 kg
Usb Compatible	No

Input

Network Frequency	40...70 Hz
Number Of Input Connectors	1 hard wire 4-wire (3P + E) 1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	340...460 V 400 V
Maximum Input Current	54 A
Max Short Time Withstand Current	65 kA
Input Harmonic Distortion	Less than 3 % for full load

Output

Maximum Configurable Power In W	40 kW
Harmonic Distortion	Less than 5 %
Output Frequency	50 Hz sync to mains 60 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised
Crest Factor	2.5
Wave Type	Sine wave
Output Voltage Tolerance	+/-1% after 50ms
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Bypass Type	Built-in static bypass
Maximum Configurable Power In Va	40 kVA

Conformance

Product Certifications	UL 1778 5th edition
Standards	CSA C22.2 No 107.3 EN/IEC 62040-1 EN/IEC 62040-2 EN/IEC 62040-3 IEC 60721-4-2 level 2M2

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3281 ft

Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0.00...3048.00 m
Acoustic Level	61 dBA
Heat Dissipation	4658 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Control Panel	Touch screen LCD user interface

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	168 cm
Package 1 Width	99 cm
Package 1 Length	64 cm
Package 1 Weight	490 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)