

Product data sheet

Specifications



Panel PC Universal - Flash Disk SSD - 12" - AC - 0 slot - fanless

HMIPUF6A0701

⚠ Discontinued on: Jun 28, 2019

⚠ End-of-service on: Apr 21, 2021

⚠ Discontinued

Main

Range Of Product	Harmony iPC
Product Or Component Type	PC panel
Processor Name	Intel icore 3rd generation 827E cache 3 MB
Chipset Type	Intel BD82HM76
Display Size	12 inch
Display Colour	16 million colours
Luminance	375 cd/m²
Video Controller Type	Intel HD Graphics 3000
Operating System	Windows 7 64 bits Ultimatemulti-language
Software Package	Vijeo Designer run time demo
Bezel Material	Aluminium alloy

Complementary

Terminal Type	Touchscreen display
Data Storage Equipment	>= 60 GB Flash disk SSD with MLC technology 2000000 h mtbf
Display Type	Active matrix colour TFT LCD with LED backlight
Display Resolution	1024 x 768 pixels XGA
Backlight Lifespan	50000 hours at 25 °C
View Angle Horizontal X Vertical	80 x 80°
Touch Panel	Analogue resistive
Memory Type	2 GB, expandable to 16 GB RAM DDR3
Type Of Cooling	Fanless
Integrated Connection Type	2 Ethernet port - RJ45 COM1 serial link - male SUB-D 9 - RS232C (rate: 115 kbit/s)bottom COM2 serial link - male SUB-D 9 - RS232C (rate: 115 kbit/s)bottom DVI video portbottom audio output - mini-jack USB 2.0 type A (rate: 480 Mbit/s)front panel 4 USB 3.0 type A (rate: 5 Gbit/s)bottom
Port Ethernet	10BASE-T/100BASE-T/1000BASE-T
[Us] Rated Supply Voltage	100...240 V AC power supply
Network Frequency	45...65 Hz
[In] Rated Current	0.6...2 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Inrush Current	20 A
Material	Die cast aluminium
Display Material	Polyethylene sheet
Fixing Mode	Enclosure door: by fixing kit (fasteners included)
Type Of Installation	Indoor
Control Type	ON/OFF push-button (equipment ON and OFF) Push-button (reset)
Local Signalling	Buzzer LED (multi-colour) for power LED (orange) for accessing Flash disk SSD (DISK) LED for link status LED for RUN
Width	313 mm
Height	239 mm
Depth	60 mm
Cut-Out Dimensions	301.5 (+ 1/- 0) x 227.5 (+ 1/- 0) x 1.6...9 mm
Net Weight	4 kg
Main Type	Universal

Environment

Ip Degree Of Protection	IP65 front panel: conforming to EN/IEC 60529
Nema Degree Of Protection	NEMA 4X front panel
Product Certifications	CULus 508 CULus CSA 22-2 No 142 CULus HazLoc Class I Division 2 UL 1604 CULus HazLoc Class I Division 2 ANSI/ISA 12-12-01 CULus HazLoc Class I Division 2 CSA 22-2 No 213 GOST CE C-Tick
Pollution Degree	2 conforming to EN/IEC 61131-2
Electromagnetic Compatibility	Immunity to electromagnetic emissions, class A conforming to EN 55022 Immunity to electromagnetic emissions, class A conforming to EN 55011 Immunity to high frequency interference conforming to EN/IEC 61131-2 Immunity to high frequency interference conforming to EN/IEC 61000-4-x
Ambient Air Temperature For Operation	0...50 °C vertical installation conforming to UL 508 0...45 °C vertical installation when using Gigabit Ethernet with HDD storage device conforming to UL 508 0...50 °C vertical installation conforming to IEC 61132-2 0...45 °C vertical installation when using Gigabit Ethernet with HDD storage device conforming to IEC 61132-2
Ambient Air Temperature For Storage	-20...60 °C conforming to IEC 60068-2-2 test Bb -20...60 °C conforming to IEC 60068-2-14 test Na
Relative Humidity	10...85 % non-condensing conforming to EN/IEC 60068-2-78 10...85 % non-condensing conforming to EN/IEC 60068-2-30
Operating Altitude	2000 m conforming to EN/IEC 61131-2
Vibration Resistance	1.75 mm (f = 2...9 Hz) continuous conforming to EN/IEC 60068-2-6 Fc 3.5 mm (f = 2...9 Hz) intermittently conforming to EN/IEC 60068-2-6 Fc 0.5 gn (f = 9...200 Hz) continuous conforming to EN/IEC 60068-2-6 Fc 1 gn (f = 9...200 Hz) intermittently conforming to EN/IEC 60068-2-6 Fc 1 mm (f = 3...13.2 Hz) continuous conforming to EN/IEC 60068-2-6 Fc 0.7 gn (f = 13.2...100 Hz) continuous conforming to EN/IEC 60068-2-6 Fc
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27, Ea tests

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.5 cm
Package 1 Width	34.5 cm
Package 1 Length	44.5 cm
Package 1 Weight	6.119 kg

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	



Dimensions Drawings

Dimensions




Mounting and Clearance


Spacing Requirement

Top, Bottom and Rear Sides	Left and Right Sides
<div><p>1 Air out</p><p>2 Air in</p></div>	<div></div>

Mounting Orientation



Panel Cut Dimensions



1 Installation panel

A	B	C
301.5 +1/0 mm (11.87 +0.04/0 in.)	227.5 +1/0 mm (8.96 +0.04/0 in.)	1.6...9 mm (0.06...0.35 in.)