

Product data sheet

Specifications



Thorsman - cable tie - natural - 3.6 x 200 mm

IMT46149

 **Discontinued on:** Sep 30, 2023

 **Discontinued**

Main

Product Range	Thorsman
Range Of Product	Thorsman
Product Type	Cable tie
Colour	Natural
Quantity Per Package	Set of 100

Complementary

Minimum Tightening Diameter	3.5 mm
Maximum Tightening Diameter	46 mm
Condition Of Use	Indoor
Resistance To Tearing	Resistance to tearing: 180 N
Material	PA (polyamide) 6.6 UV-stabilised
Length	200 mm
Width	3.6 mm
Net Weight	0.082 kg
Market Segment	Small commercial

Environment

Environmental Characteristic	Fire resistance needle flame 30 s conforming to IEC 60695-11-5
Flame Retardance	Self-extinguishing conforming to UL 94 V2
Ambient Air Temperature For Operation	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.12 cm
Package 1 Width	3.6 cm
Package 1 Length	26 cm
Package 1 Weight	0.82 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations