

# Product data sheet

Specifications



## Canalis - Cu length for plug-in tap-off unit - 1600A - 3L+N+PER - 2m standard

KTC1600ED720

ⓘ Discontinued

### Main

Range	Canalis
Product Name	KT
Product Or Component Type	Busbar trunking
Busbar Description	Distribution length
Device Short Name	KTC
Device Application	High power distribution
Material	Copper
[Ie] Rated Operational Current	1600 A at 35 °C
Polarity	3L + N + PER
Number Of Tap-Off Outlets	3
Nominal Output Current	25...630 A
Earth Conductor	Reinforced
Short-Circuit Level	Reinforced version
Length	2000 mm
Provided Equipment	Jointing unit Trunking unit

### Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	85 kA
[Ipk] Rated Peak Withstand Current	187 kA
Electrical Connection	Sliding contact
Radiated Magnetic Field	0.75 µT
Thermal Stress Limit	7225000 kA².s
Thdi	0...15 % 1600 A 15...33 % 1350 A 33...100 % 1000 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Voltage Drop	<0.0027 V with power factor = 0.7 at 50 Hz with 1A for 100 m long <0.0026 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0029 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0028 V with power factor = 0.8 at 50 Hz with 1A for 100 m long
Mounting Mode	By hook
Mounting Support	Cantilever arm Pendant
Installation Direction	Vertical Horizontal
Neutral Position	Right
Tap-Off Unit Interval	500 mm
Standards	IEC 61439-6 IEC 61439-1
Dimension Type	Fix
Width	140 mm
Height	124 mm
Colour	White (RAL 9001)
Net Weight	78 kg
Linear Load	39 kg/m

## Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	0...35 °C (100 % of In) 35...40 °C (95 % of In) 40...45 °C (90 % of In) 45...50 °C (84 % of In) 50...55 °C (79 % of In)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**Environmental Disclosure**

[Product Environmental Profile](#)