

# Product data sheet

Specifications

## Mureva Tube GT HF - bend - diam. 25 - black - IP30



IMT49021

### Main

Range Of Product	Mureva
Product Or Component Type	Bend
Mounting Location	Indoor Outdoor
Nominal Cross Section	314 mm²
Diameter	External: 25 mm Internal: 20 mm
Colour Tint	Black (RAL 9005)

### Complementary

Quantity Per Set	10 pieces
Ambient Air Temperature For Operation	-25...95 °C
Material	PC/ABS
Standards	IEC 61386

### Environment

Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07
Environmental Characteristic	Non-flame propagating

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.2 cm
Package 1 Width	17 cm
Package 1 Length	29.2 cm
Package 1 Weight	0.001 g

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations