

# Product data sheet

Specifications



## OptiLine 50 - pole - tension-mounted - four installation boxes - white

INS40445

⚠ Discontinued on: Jul 21, 2021

⚠ End-of-service on: Feb 2, 2022

⚠ Discontinued

### Main

Range	OptiLine
Product Name	OptiLine 50
Product Type	Pole
Type Of Pole	Four installation boxes
Configuration	Pre-defined, pre-wired
Additional Information	Adjustability of ceiling fixing 400 mm
Colour	White (RAL 9010)
Quantity Package 1 / Unit	Set of 1
Cover Type	4 closed cover cover 50 mm in plastic
Cover Plate Colour Tint	White (RAL 9010)

### Complementary

Pole/Post Surface Finish	Powder coated
Fixing Mode	Tension-mounted
Product Material	Aluminium
Number Of Data Socket Outlets	8 x RJ45 Cat.6 UTP
Product Material	Aluminium
Height	2700...3100 mm
Width	149 mm
Shape	Round
Adjustment	Adjustable in height: 400 mm
Useful Cross Section	2535 mm <sup>2</sup>
Compartment Partitioning	4 compartments

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	310 cm
Package 1 Width	14.9 cm
Package 1 Length	14 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1 kg
------------------	------

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations