

Product data sheet

Specifications



Double Pole Switch, Vivace, 20A, 250V, 2 gang, with neon indicator, white

KB32D20NE

Main

Range	Vivace
Product Or Component Type	Switch
Device Short Name	KB32
Device Application	Control switch
Additional Switch Application	On/off switching
Number Of Rocker	2
Switch Function	Double 1-way
Colour Tint	Surround: white Base: white

Complementary

Technology Type	Electromechanical
Device Presentation	Complete product
Actuator	Rocker
Pilot Light	Neon indicator lamp
Number Of Gangs	2 gangs
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Surface Finish	Glossy
Surface Treatment	Untreated
[Ue] Rated Operational Voltage	220...250 V
Type Of Packing	Plastic bag
Network Type	AC
Quantity Per Set	1
Sale Per Indivisible Quantity	1
Rated Current	20 A
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Screw terminal
Embedding Depth	20 mm
Number Of Terminals	10
Rated Current	20 A at 250 V AC, inductive 20 A at 250 V AC, resistive
[Ue] Rated Operational Voltage	250 V AC
Network Frequency	50/60 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	10 screw terminals
Terminal Identifier	L1 N2 N1 L2
Tightening Torque	0.4 N.m
Clamping Connection Capacity	<= 4 mm² for rigid or stranded cable(s)
Wire Stripping Length	12 mm
Width	86 mm
Height	86 mm
Depth	32 mm

Environment

Standards	IEC 60669-1 SS 227 MS IEC 60669-1
Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	122.5 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations