


Product data sheet

Specifications



Reduction unit, Canalis KRA,
aluminium, 3200A, 3L, fixed length
1m, fire rated, grey RAL7030

KRA3200RU3

Main

Range	Canalis
Product Name	KR
Product Or Component Type	Reducer
Busbar Description	Fire rated
Device Short Name	KRA
Range Compatibility	Canalis KRA Canalis KTA
Material	Aluminium
[Ie] Rated Operational Current	3200 A at 35 °C
Polarity	3L
Length	1000 mm

Complementary

Accessory / Separate Part Category	Adaptation accessory
Housing Material	Mineral epoxy resin
Contacts Material	Tinned aluminium
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	100 kA
[Ipk] Rated Peak Withstand Current	220 kA
Radiated Magnetic Field	37.09 mT
Thermal Stress Limit	10000000 kA².s
Maximum Voltage Drop	<0.0033 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0048 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0051 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0053 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Location	Indoor use only
Installation Direction	Vertical Horizontal
Product Certifications	CE ATEX EAC
Standards	IEC 61439-6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	100 mm
Height	460 mm
Colour	Grey (RAL 7030)
Linear Load	85 kg/m

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Pollution Degree	3
Fire Resistance	760 °C 180 min conforming to IEC 60331-1
Derating Factor	0...35 °C (100 % of In) 35...40 °C (96 % of In) 40...45 °C (89 % of In) 45...50 °C (84 % of In) 50...55 °C (78 % of In)
Operating Altitude	1000 m 100 % of In (indoor) 2000 m 99 % of In (indoor) 3000 m 96 % of In (indoor) 4000 m 90 % of In (indoor) 1000 m 98 % of In (outdoor) 2000 m 94 % of In (outdoor) 3000 m 89 % of In (outdoor) 4000 m 83 % of In (outdoor)
Environmental Characteristic	EMC directive conforming to IEC 61439-6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	38 cm
Package 1 Width	10 cm
Package 1 Length	100 cm
Package 1 Weight	89.25 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information