


# Product data sheet

Specifications



Straight expansion unit, Canalis  
KTA, aluminium, 2000A, 3L+N+PER  
(Al), fixed length 1m, white RAL9001

KTA2000DB510

## Main

Range	Canalis
Product Name	KT
Product Or Component Type	Expansion unit
Busbar Description	Flexible bar
Device Short Name	KTA
Device Application	Feeder length
Material	Aluminium
[Ie] Rated Operational Current	2000 A at 35 °C
Polarity	3L + N + PER
Number Of Tap-Off Outlets	0
Length	1000 mm
Provided Equipment	Trunking unit Jointing unit

## Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	70 kA
[Ipk] Rated Peak Withstand Current	154 kA
Radiated Magnetic Field	1.3 µT
Thermal Stress Limit	4900000 kA².s
Thdi	0...15 % 2000 A 15...33 % 2500 A 33...100 % 3200 A
Maximum Voltage Drop	<0.0029 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.003 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0029 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0027 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Mode	By hook
Mounting Support	Cantilever arm Pendant

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Installation Direction	Horizontal Vertical
Horizontal Distance	30 m
Neutral Position	Right
Standards	IEC 61439-1 IEC 61439-6
Dimension Type	Fix
Width	140 mm
Height	204 mm
Colour	White (RAL 9001)
Net Weight	26 kg
Linear Load	26 kg/m

## Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	0...35 °C (100 % of In) 35...40 °C (97 % of In) 40...45 °C (93 % of In) 45...50 °C (90 % of In) 50...55 °C (86 % of In)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	24.0 cm
Package 1 Length	100.0 cm
Package 1 Weight	32.0 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)