


Product data sheet

Specifications



Straight transport length, Canalis KTA, aluminium, 2500A, 3L+N+PER (Cu), high Icw, made to measure 2-2.5m, RAL9001

KTA2500ET72C

Main

Range	Canalis
Product Name	KT
Product Or Component Type	Busbar trunking
Busbar Description	Transport length
Device Short Name	KTA
Device Application	Feeder length
Material	Aluminium
[Ie] Rated Operational Current	2500 A at 35 °C
Polarity	3L + N + PER
Number Of Tap-Off Outlets	0
Earth Conductor	Reinforced
Short-Circuit Level	Reinforced version
Length	2001...2500 mm
Provided Equipment	Jointing unit Trunking unit

Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	113 kA
[Ipk] Rated Peak Withstand Current	248 kA
Radiated Magnetic Field	1.6 µT
Thermal Stress Limit	12769000 kA².s
Thdi	0...15 % 2500 A 15...33 % 3200 A 33...100 % 4000 A
Maximum Voltage Drop	<0.0024 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0025 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0024 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0022 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Mode	By hook

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Support	Cantilever arm Pendant
Installation Direction	Horizontal Vertical
Neutral Position	Right
Standards	IEC 61439-6 IEC 61439-1
Dimension Type	Made to measure
Width	146 mm
Height	274 mm
Colour	White (RAL 9001)
Linear Load	36 kg/m

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	0...35 °C (100 % of In) 35...40 °C (97 % of In) 40...45 °C (93 % of In) 45...50 °C (90 % of In) 50...55 °C (86 % of In)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	695.96 cm
Package 1 Width	14.6 cm
Package 1 Length	250.0 cm
Package 1 Weight	94.5 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)