


Product data sheet

Specifications



Edgewise and flat zed unit, Canalis KTC, copper, 1600A, 3L+PE, made to measure, neutral N4, white RAL9001

KTC1600CP34

Main

Range	Canalis
Product Name	KT
Product Or Component Type	Multiple elbow
Busbar Description	Standard
Device Short Name	KTC
Device Application	Change direction
Material	Copper
[Ie] Rated Operational Current	1600 A at 35 °C
Polarity	3L + PE
Direction Change Type	direction 2: edgewise to upward direction 1: flat to left
Operating Angle	90 °
Earth Conductor	Standard earth
Short-Circuit Level	Standard version
Provided Equipment	Trunking unit Jointing unit

Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	65 kA
[Ipk] Rated Peak Withstand Current	143 kA
Radiated Magnetic Field	0.75 µT
Thermal Stress Limit	4225000 kA².s
Thdi	0...15 % 1600 A 15...33 % 1350 A 33...100 % 1000 A
Maximum Voltage Drop	<0.0027 V with power factor = 0.7 at 50 Hz with 1A for 100 m long <0.0026 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0029 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0028 V with power factor = 0.8 at 50 Hz with 1A for 100 m long

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Neutral Position	Left
Standards	IEC 61439-6 IEC 61439-1
Dimension Type	Made to measure
Width	140 mm
Height	direction 2: 220...599 mm
Colour	White (RAL 9001)
Length	direction 1: 300 mm direction 3: 300 mm
Linear Load	29 kg/m

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	0...35 °C (100 % of In) 35...40 °C (95 % of In) 40...45 °C (90 % of In) 45...50 °C (84 % of In) 50...55 °C (79 % of In)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	34.2 cm
Package 1 Width	35.0 cm
Package 1 Length	73.2 cm
Package 1 Weight	48.2 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)