

Product data sheet

Specifications



TeSys F - suppressor module - varistor (peak limiting) - 24...48 V AC/DC

LA4FVE

Main

Range	TeSys
Device Short Name	LA4F
Product Or Component Type	Suppressor module
Product Compatibility	LC1F

Complementary

Mounting Mode	By clips
Suppressor Technology	Varistor (peak limiting)
[Uc] Control Circuit Voltage	24...48 V AC 24...48 V DC
Maximum Peak Voltage	2 Uc
Net Weight	0.04 kg

Environment

Product Certifications	UKCA
------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	5.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	47.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	70
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.721 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations