


# Product data sheet

Specifications



## bar-mounted contactor - TeSys LC1-BR - 3P - AC-3 1000 V 2750 A - coil 110 VAC

LC1BR33F13

 **Discontinued on:** Sep 28, 2021

 **Discontinued**

### Main

Range	TeSys
Product Name	TeSys B
Product Or Component Type	Contactors
Device Short Name	LC1BR
Contactors Application	Motor-heating-lighting
Utilisation Category	AC-1 AC-3
Control Circuit Type	AC
Coil Type	Standard
Poles Description	3P
Pole Contact Composition	3 NO
[Ie] Rated Operational Current	2750 A (at <40 °C) AC AC-1 for power circuit 1800 A (at <40 °C) AC AC-3 for power circuit
Motor Power Kw	500 kW at 220...230 V AC 50/60 Hz 750 kW at 1000 V AC 50/60 Hz 900 kW at 380...400 V AC 50/60 Hz 900 kW at 415 V AC 50/60 Hz 900 kW at 440 V AC 50/60 Hz 900 kW at 500 V AC 50/60 Hz 900 kW at 660...690 V AC 50/60 Hz
Auxiliary Contact Composition	1 NO + 3 NC
[Uc] Control Circuit Voltage	110 V AC 50...400 Hz

### Complementary

Protective Cover	With
Auxiliary Contacts Type	type instantaneous 1 NO + 3 NC
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc Drop-out: 0.4...0.5 Uc
[Ui] Rated Insulation Voltage	1000 V - for power circuit conforming to IEC 60158-1 1000 V - for power circuit conforming to IEC 60947-4 1500 V - for power circuit conforming to VDE 0110 group C
Connections - Terminals	Power circuit: bars 4 x - busbar cross section: 100 x 5 mm
Tightening Torque	Power circuit: 35 N.m - on bars
[Ue] Rated Operational Voltage	Power circuit: <= 1000 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	2750 A (at 40 °C) for power circuit

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Irms Rated Making Capacity</b>	18000 A at 1000 V AC for power circuit conforming to IEC 60158-1 18000 A at 1000 V AC for power circuit conforming to IEC 60947-4
<b>Rated Breaking Capacity</b>	11000 A at 660...690 V for power circuit conforming to IEC 60158-1 11000 A at 660...690 V for power circuit conforming to IEC 60947-4 15000 A at 500 V for power circuit conforming to IEC 60158-1 15000 A at 500 V for power circuit conforming to IEC 60947-4 18000 A at 440 V for power circuit conforming to IEC 60158-1 18000 A at 440 V for power circuit conforming to IEC 60947-4 6000 A at 1000 V for power circuit conforming to IEC 60158-1 6000 A at 1000 V for power circuit conforming to IEC 60947-4
<b>Associated Fuse Rating</b>	2000 A aM at <= 440 V for power circuit 2400 A gI at <= 440 V for power circuit
<b>Average Impedance</b>	0.09 mOhm - lth 2750 A 50 Hz for power circuit
<b>Power Dissipation Per Pole</b>	680 W AC-1 - lth 2750 A
<b>Inrush Power In Va</b>	1300 VA
<b>Hold-In Power Consumption In Va</b>	31 VA
<b>Operating Time</b>	100...150 ms closing 20...40 ms opening
<b>Mechanical Durability</b>	1200000 cycles
<b>Maximum Operating Rate</b>	120 cyc/h 55 °C
<b>Rated Operational Power In Va</b>	2000 VA at 110...127 V AC-1 - electrical durability: 1000000 cycles - for control circuit 2000 VA at 110...127 V AC-3 - electrical durability: 1000000 cycles - for control circuit 3500 VA at 500 V AC-1 - electrical durability: 1000000 cycles - for control circuit 3500 VA at 500 V AC-3 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 220 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 220 V AC-3 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 380 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 380 V AC-3 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 415...440 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 415...440 V AC-3 - electrical durability: 1000000 cycles - for control circuit
<b>Rated Operational Power In W</b>	200 W at 500 V AC - electrical durability: 1000000 cycles - for control circuit 230 W at 440 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 110 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 220 V AC - electrical durability: 1000000 cycles - for control circuit
<b>Height</b>	555 mm
<b>Width</b>	475 mm
<b>Depth</b>	915 mm
<b>Net Weight</b>	129 kg

## Environment

<b>Standards</b>	BS 5424 NF C 63-110 IEC 60158-1 VDE 0660 IEC 60947-4
<b>Product Certifications</b>	CSA BV RINA
<b>Protective Treatment</b>	TC TH
<b>Ambient Air Temperature For Operation</b>	-5...55 °C
<b>Ambient Air Temperature For Storage</b>	-60...80 °C
<b>Operating Altitude</b>	3000 m without derating

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	58 cm
Package 1 Width	66 cm
Package 1 Length	120 cm
Package 1 Weight	139 kg

## Contractual warranty

Warranty	18 months
----------	-----------