

Product data sheet

Specifications



Contactor, Easy TeSys
Control, LC1E,
3P(3NO), AC-3, <=440V, 40A, 220V
AC coil, 50Hz

LC1E40M5

Main

Range	Easy TeSys
Range Of Product	Easy TeSys Control
Product Or Component Type	Contactor
Device Short Name	LC1E
Contactor Application	Motor control Resistive load
Utilisation Category	AC-1 AC-3
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 50/60 Hz
[Ie] Rated Operational Current	40 A (at <55 °C) at <= 440 V AC AC-3 for power circuit 60 A (at <60 °C) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	220 V AC 50 Hz

Complementary

Motor Power Kw	18.5 kW at 380...400 V 11 kW at 220...230 V AC 50/60 Hz 22 kW at 415 V 22 kW at 440 V 22 kW at 500 V 30 kW at 660...690 V
Pole Contact Composition	3 NO
[Ith] Conventional Free Air Thermal Current	60 A (at 55 °C)
Irms Rated Making Capacity	400 A at 440 V AC for power circuit conforming to IEC 60947-4-1
Rated Breaking Capacity	320 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	320 A 40 °C - 10 s for power circuit 165 A 40 °C - 60 s for power circuit 72 A 40 °C - 600 s for power circuit
Associated Fuse Rating	10 A gG at <= 690 V coordination type 1 for control circuit conforming to IEC 60947-5-1 80 A gG at <= 690 V coordination type 1 for power circuit
Average Impedance	1.5 mOhm - Ith 60 A 50 Hz for power circuit
Power Dissipation Per Pole	2.4 W AC-3 5.4 W AC-1
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Uimp] Rated Impulse Withstand Voltage	6 kV coil not connected to the power circuit conforming to IEC 60947
Mechanical Durability	5000000 cycles
Electrical Durability	350000 cycles AC-1 900000 cycles AC-3
Control Circuit Type	AC at 50 Hz
Control Circuit Voltage Limits	0.85...1.1 Uc (-5...55 °C):operational 50 Hz 0.3...0.6 Uc (-5...55 °C):drop-out 50 Hz
Inrush Power In Va	160 VA 50 Hz cos phi 0.75 (at 20 °C) 140 VA 60 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	15 VA 50 Hz cos phi 0.3 (at 20 °C) 13 VA 60 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	6...10 W for control circuit
Operating Time	20...26 ms on closing 8...12 ms on opening
Maximum Operating Rate	1200 cyc/h 55 °C
Connections - Terminals	Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 2.5...25 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 2.5...10 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 2.5...25 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 2.5...16 mm ² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 5 N.m
Auxiliary Contact Composition	1 NO + 1 NC
Minimum Switching Voltage	17 V for control circuit
Minimum Switching Current	5 mA for control circuit
Insulation Resistance	> 10 MOhm for control circuit
Non-Overlap Time	1.5 ms on energisation guaranteed between NC and NO contact 1.5 ms on de-energisation guaranteed between NC and NO contact
Mounting Support	Plate DIN rail

Environment

Standards	IEC 60947-1 IEC 60947-4-1 IEC 60947-5-1
Product Certifications	EAC CE
Ip Degree Of Protection	IP2X conforming to IEC 60529
Protective Treatment	TH (pollution degree 3) conforming to IEC 60068-2-30 test Db

Permissible Ambient Air Temperature Around The Device	-20...70 °C at Uc -60...80 °C storage -5...55 °C operation
Operating Altitude	3000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Mechanical Robustness	Vibrations contactor open (1.5 Gn, 5...300 Hz) Vibrations contactor closed (3 Gn, 5...300 Hz) Shocks contactor open (6 Gn for 11 ms) Shocks contactor closed (7 Gn for 11 ms)
Height	127 mm
Width	75 mm
Depth	114 mm
Net Weight	0.98 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	12.4 cm
Package 1 Length	13.4 cm
Package 1 Weight	975.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9.168 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information