

Product data sheet

Specifications



TeSys F contactor - 3P (3 NO) - AC-3 - <= 440 V 115 A - coil 415 V AC

LC1F115N7

 To be discontinued on: Dec 31, 2025

 To be discontinued

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load Motor control
Utilisation Category	AC-1 AC-4 AC-3
Poles Description	3P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	415 V AC 40...400 Hz
[Ie] Rated Operational Current	200 A (at <40 °C) at <= 440 V AC-1 115 A (at <55 °C) at <= 440 V AC-3

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	200 A (at 40 °C)
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1100 A 40 °C - 10 s 640 A 40 °C - 30 s 520 A 40 °C - 1 min 400 A 40 °C - 3 min 320 A 40 °C - 10 min
Associated Fuse Rating	125 A aM at <= 440 V 200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1 5 W AC-3
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Motor Power Kw	55 kW at 380...400 V AC 50/60 Hz (AC-3) 59 kW at 415 V AC 50/60 Hz (AC-3) 59 kW at 440 V AC 50/60 Hz (AC-3) 75 kW at 500 V AC 50/60 Hz (AC-3) 80 kW at 660...690 V AC 50/60 Hz (AC-3) 30 kW at 220...230 V AC 50/60 Hz (AC-3) 18.5 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc 40...400 Hz (at 55 °C) Drop-out: 0.2...0.55 Uc 40...400 Hz (at 55 °C)
Mechanical Durability	10 Mcycles
Inrush Power In Va	770 VA, 40...400 Hz cos phi 0.9 (at 20 °C)
Hold-In Power Consumption In Va	8.1 VA, 40...400 Hz cos phi 0.9 (at 20 °C)
Maximum Operating Rate	2400 cyc/h 55 °C
Operating Time	35 ms closing (at Uc) 130 ms opening (at Uc)
Connections - Terminals	Power circuit: bar 2 cable(s) - busbar cross section: 20 x 3 mm Power circuit: lugs-ring terminals 1 cable(s) 95 mm² Power circuit: connector 1 cable(s) 95 mm² Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²solid without cable end Power circuit: bolted connection
Tightening Torque	Power circuit: 10 N.m Control circuit: 1.2 N.m
Mounting Support	Plate
Heat Dissipation	5.9...7.2 W
Standards	EN 60947-4-1 IEC 60947-4-1 JIS C8201-4-1 IEC 60947-1 EN 60947-1
Product Certifications	RMRoS LROS (Lloyds register of shipping) RINA UL CB DNV BV CCC ABS UKCA
Compatibility Code	LC1F
Control Circuit Type	AC at 40...400 Hz

Environment

Ip Degree Of Protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Protective Treatment	TH
Ambient Air Temperature For Operation	-40...60 °C
Ambient Air Temperature For Storage	-60...80 °C
Permissible Ambient Air Temperature Around The Device	60...70 °C at Uc
Height	162 mm
Width	163.3 mm

Depth	171 mm
Operating Altitude	3000 m without derating
Net Weight	3.43 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.500 cm
Package 1 Width	19.500 cm
Package 1 Length	22.500 cm
Package 1 Weight	3.982 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	16.565 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	16
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	74.260 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov