

Product data sheet

Specifications

Schneider Electric LC1F150MD

Image

⚠ Discontinued

TeSys F contactor - 3P (3 NO)
- AC-3 - <= 440 V 250 A - coil
220 V DC

LC1F150MD

⚠ Discontinued on: Dec 26, 2023

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-4 AC-1
Poles Description	3P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	220 V DC
[Ie] Rated Operational Current	250 A (at <40 °C) at <= 440 V AC-1 150 A (at <55 °C) at <= 440 V AC-3

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	250 A (at 40 °C)
Rated Breaking Capacity	1200 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1200 A 40 °C - 10 s 700 A 40 °C - 30 s 600 A 40 °C - 1 min 450 A 40 °C - 3 min 350 A 40 °C - 10 min
Associated Fuse Rating	160 A aM at <= 440 V 250 A gG at <= 440 V
Average Impedance	0.35 mOhm - Ith 250 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power Dissipation Per Pole	22 W AC-1 8 W AC-3
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Motor Power Kw	75 kW at 380...400 V AC 50/60 Hz (AC-3) 80 kW at 415 V AC 50/60 Hz (AC-3) 80 kW at 440 V AC 50/60 Hz (AC-3) 90 kW at 500 V AC 50/60 Hz (AC-3) 100 kW at 660...690 V AC 50/60 Hz (AC-3) 40 kW at 220...230 V AC 50/60 Hz (AC-3) 22 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.15...0.2 Uc (at 55 °C)
Mechanical Durability	10 Mcycles
Inrush Power In W	560 W (at 20 °C)
Hold-In Power Consumption In W	4.5 W at 20 °C
Maximum Operating Rate	2400 cyc/h 55 °C
Operating Time	30...40 ms closing 30...50 ms opening
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²solid without cable end Power circuit: bar 2 cable(s) - busbar cross section: 25 x 3 mm Power circuit: lugs-ring terminals 1 cable(s) 120 mm² Power circuit: connector 1 cable(s) 120 mm² Power circuit: bolted connection
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 18 N.m
Mounting Support	Plate
Heat Dissipation	4.5 W
Standards	IEC 60947-4-1 JIS C8201-4-1 IEC 60947-1 EN 60947-4-1 EN 60947-1
Product Certifications	BV DNV UL CB RMRoS RINA ABS CCC LROS (Lloyds register of shipping) UKCA
Compatibility Code	LC1F
Control Circuit Type	DC standard

Environment

Ip Degree Of Protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Protective Treatment	TH
Ambient Air Temperature For Operation	-40...60 °C
Ambient Air Temperature For Storage	-60...80 °C
Permissible Ambient Air Temperature Around The Device	60...70 °C at Uc
Height	170 mm
Width	163.5 mm

Depth	171 mm
Operating Altitude	3000 m without derating
Net Weight	3.43 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.5 cm
Package 1 Width	20.0 cm
Package 1 Length	24.0 cm
Package 1 Weight	4.25 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov