

# Product data sheet

Specifications



Contactor, TeSys Deca, 3P(3NO),  
AC-3/AC-3e, <=440V, 25A, 230V  
AC 50/60Hz coil, screw clamp  
terminals

LC1D25P7

## Main

|                                |   |
|--------------------------------|---|
| Range Of Product               | TeSys Deca  |
| Product Or Component Type      | Contactor   |
| Device Short Name              | LC1D  |
| Contactor Application          | Resistive load<br>Motor control   |
| Utilisation Category           | AC-3<br>AC-4<br>AC-1<br>AC-3e   |
| Poles Description              | 3P  |
| [Ue] Rated Operational Voltage | Power circuit: <= 690 V AC 25...400 Hz<br>Power circuit: <= 300 V DC  |
| [Ie] Rated Operational Current | 25 A (at <60 °C) at <= 440 V AC AC-3 for power circuit<br>40 A (at <60 °C) at <= 440 V AC AC-1 for power circuit<br>25 A (at <60 °C) at <= 440 V AC AC-3e for power circuit |
| [Uc] Control Circuit Voltage   | 230 V AC 50/60 Hz   |

## Complementary

|   |   |
|---|---|
| Motor Power Kw                              | 5.5 kW at 220...230 V AC 50/60 Hz (AC-3)<br>11 kW at 380...400 V AC 50/60 Hz (AC-3)<br>11 kW at 415...440 V AC 50/60 Hz (AC-3)<br>15 kW at 500 V AC 50/60 Hz (AC-3)<br>15 kW at 660...690 V AC 50/60 Hz (AC-3)<br>5.5 kW at 400 V AC 50/60 Hz (AC-4)<br>5.5 kW at 220...230 V AC 50/60 Hz (AC-3e)<br>11 kW at 380...400 V AC 50/60 Hz (AC-3e)<br>11 kW at 415...440 V AC 50/60 Hz (AC-3e)<br>15 kW at 500 V AC 50/60 Hz (AC-3e)<br>15 kW at 660...690 V AC 50/60 Hz (AC-3e) |
| Motor Power Hp                              | 3 hp at 230/240 V AC 50/60 Hz for 1 phase motors<br>2 hp at 115 V AC 50/60 Hz for 1 phase motors<br>7.5 hp at 230/240 V AC 50/60 Hz for 3 phases motors<br>15 hp at 460/480 V AC 50/60 Hz for 3 phases motors<br>20 hp at 575/600 V AC 50/60 Hz for 3 phases motors<br>7.5 hp at 200/208 V AC 50/60 Hz for 3 phases motors  |
| Compatibility Code                          | LC1D  |
| Pole Contact Composition                    | 3 NO  |
| Protective Cover                            | With  |
| [Ith] Conventional Free Air Thermal Current | 10 A (at 60 °C) for signalling circuit<br>40 A (at 60 °C) for power circuit   |
| Irms Rated Making Capacity                  | 140 A AC for signalling circuit conforming to IEC 60947-5-1<br>250 A DC for signalling circuit conforming to IEC 60947-5-1<br>450 A at 440 V for power circuit conforming to IEC 60947  |
| Rated Breaking Capacity                     | 450 A at 440 V for power circuit conforming to IEC 60947  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|   |   |
|---|---|
| <b>[Icw] Rated Short-Time Withstand Current</b> | 240 A 40 °C - 10 s for power circuit<br>380 A 40 °C - 1 s for power circuit<br>50 A 40 °C - 10 min for power circuit<br>120 A 40 °C - 1 min for power circuit<br>100 A - 1 s for signalling circuit<br>120 A - 500 ms for signalling circuit<br>140 A - 100 ms for signalling circuit |
| <b>Associated Fuse Rating</b>                   | 10 A gG for signalling circuit conforming to IEC 60947-5-1<br>63 A gG at <= 690 V coordination type 1 for power circuit<br>40 A gG at <= 690 V coordination type 2 for power circuit  |
| <b>Average Impedance</b>                        | 2 mOhm - lth 40 A 50 Hz for power circuit   |
| <b>Power Dissipation Per Pole</b>               | 3.2 W AC-1<br>1.25 W AC-3<br>1.25 W AC-3e   |
| <b>[Ui] Rated Insulation Voltage</b>            | Power circuit: 690 V conforming to IEC 60947-4-1<br>Power circuit: 600 V CSA certified<br>Power circuit: 600 V UL certified<br>Signalling circuit: 690 V conforming to IEC 60947-1<br>Signalling circuit: 600 V CSA certified<br>Signalling circuit: 600 V UL certified               |
| <b>Overvoltage Category</b>                     | III   |
| <b>Pollution Degree</b>                         | 3   |
| <b>[Uimp] Rated Impulse Withstand Voltage</b>   | 6 kV conforming to IEC 60947  |
| <b>Safety Reliability Level</b>                 | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1<br>B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1  |
| <b>Mechanical Durability</b>                    | 15 Mcycles  |
| <b>Electrical Durability</b>                    | 1.65 Mcycles 25 A AC-3 at Ue <= 440 V<br>1.4 Mcycles 40 A AC-1 at Ue <= 440 V<br>1.65 Mcycles 25 A AC-3e at Ue <= 440 V   |
| <b>Control Circuit Type</b>                     | AC at 50/60 Hz standard   |
| <b>Coil Technology</b>                          | Without built-in suppressor module  |
| <b>Control Circuit Voltage Limits</b>           | 0.3...0.6 Uc (-40...70 °C):drop-out AC 50/60 Hz<br>0.8...1.1 Uc (-40...60 °C):operational AC 50 Hz<br>0.85...1.1 Uc (-40...60 °C):operational AC 60 Hz<br>1...1.1 Uc (60...70 °C):operational AC 50/60 Hz   |
| <b>Inrush Power In Va</b>                       | 70 VA 60 Hz cos phi 0.75 (at 20 °C)<br>70 VA 50 Hz cos phi 0.75 (at 20 °C)  |
| <b>Hold-In Power Consumption In Va</b>          | 7.5 VA 60 Hz cos phi 0.3 (at 20 °C)<br>7 VA 50 Hz cos phi 0.3 (at 20 °C)  |
| <b>Heat Dissipation</b>                         | 2...3 W at 50/60 Hz   |
| <b>Operating Time</b>                           | 12...22 ms closing<br>4...19 ms opening   |
| <b>Maximum Operating Rate</b>                   | 3600 cyc/h 60 °C  |

|                               |   |
|-------------------------------|---|
| Connections - Terminals       | Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: flexible without cable end<br>Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: flexible without cable end<br>Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: flexible with cable end<br>Control circuit: screw clamp terminals 2 1...2.5 mm² - cable stiffness: flexible with cable end<br>Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: solid without cable end<br>Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: solid without cable end<br>Power circuit: screw clamp terminals 1 2.5...10 mm² - cable stiffness: flexible without cable end<br>Power circuit: screw clamp terminals 2 2.5...10 mm² - cable stiffness: flexible without cable end<br>Power circuit: screw clamp terminals 1 1...10 mm² - cable stiffness: flexible with cable end<br>Power circuit: screw clamp terminals 2 1.5...6 mm² - cable stiffness: flexible with cable end<br>Power circuit: screw clamp terminals 1 1.5...10 mm² - cable stiffness: solid without cable end<br>Power circuit: screw clamp terminals 2 2.5...10 mm² - cable stiffness: solid without cable end |
| Tightening Torque             | Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2<br>Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2<br>Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2<br>Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2  |
| Auxiliary Contact Composition | 1 NO + 1 NC   |
| Auxiliary Contacts Type       | type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1<br>type mirror contact 1 NC conforming to IEC 60947-4-1  |
| Signalling Circuit Frequency  | 25...400 Hz   |
| Minimum Switching Voltage     | 17 V for signalling circuit   |
| Minimum Switching Current     | 5 mA for signalling circuit   |
| Insulation Resistance         | > 10 MOhm for signalling circuit  |
| Non-Overlap Time              | 1.5 ms on de-energisation between NC and NO contact<br>1.5 ms on energisation between NC and NO contact   |
| Mounting Support              | Rail<br>Plate   |

## Environment

|                         |  |
|-------------------------|--|
| Standards               | CSA C22.2 No 14<br>EN 60947-4-1<br>EN 60947-5-1<br>IEC 60947-4-1<br>IEC 60947-5-1<br>UL 508<br>IEC 60335-1         |
| Product Certifications  | UL<br>GL<br>CCC<br>RINA<br>GOST<br>DNV<br>BV<br>LROS (Lloyds register of shipping)<br>CSA<br>UKCA                  |
| Ip Degree Of Protection | IP20 front face conforming to IEC 60529  |
| Protective Treatment    | TH conforming to IEC 60068-2-30  |
| Climatic Withstand      | conforming to IACS E10 exposure to damp heat<br>conforming to IEC 60947-1 Annex Q category D exposure to damp heat |

|  |   |
|--|---|
| <b>Permissible Ambient Air Temperature Around The Device</b> | -40...60 °C<br>60...70 °C with derating   |
| <b>Operating Altitude</b>                                    | 0...3000 m  |
| <b>Fire Resistance</b>                                       | 850 °C conforming to IEC 60695-2-1  |
| <b>Flame Retardance</b>                                      | V1 conforming to UL 94  |
| <b>Mechanical Robustness</b>                                 | Vibrations contactor open (2 Gn, 5...300 Hz)<br>Vibrations contactor closed (4 Gn, 5...300 Hz)<br>Shocks contactor closed (15 Gn for 11 ms)<br>Shocks contactor open (8 Gn for 11 ms) |
| <b>Height</b>  | 85 mm   |
| <b>Width</b>   | 45 mm   |
| <b>Depth</b>   | 92 mm   |
| <b>Net Weight</b>  | 0.37 kg   |

## Packing Units

|                                     |            |
|-------------------------------------|------------|
| <b>Unit Type Of Package 1</b>       | PCE        |
| <b>Number Of Units In Package 1</b> | 1          |
| <b>Package 1 Height</b>             | 5.000 cm   |
| <b>Package 1 Width</b>              | 9.000 cm   |
| <b>Package 1 Length</b>             | 11.000 cm  |
| <b>Package 1 Weight</b>             | 417.000 g  |
| <b>Unit Type Of Package 2</b>       | S02        |
| <b>Number Of Units In Package 2</b> | 20         |
| <b>Package 2 Height</b>             | 15.000 cm  |
| <b>Package 2 Width</b>              | 30.000 cm  |
| <b>Package 2 Length</b>             | 40.000 cm  |
| <b>Package 2 Weight</b>             | 8.576 kg   |
| <b>Unit Type Of Package 3</b>       | P06        |
| <b>Number Of Units In Package 3</b> | 320        |
| <b>Package 3 Height</b>             | 75.000 cm  |
| <b>Package 3 Width</b>              | 80.000 cm  |
| <b>Package 3 Length</b>             | 60.000 cm  |
| <b>Package 3 Weight</b>             | 145.488 kg |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc


✓ Pvc Free

## Certifications & Standards

|                           |   |
|---------------------------|---|
| Reach Regulation          | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive         | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)   |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins   |
| Circularity Profile       | <a href="#">End of Life Information</a>   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Dimensions Drawings

Dimensions



- (1) Including LAD 4BB
- (2) Minimum electrical clearance

| LC1 |                                    | D25...D38 (3-pole) |
|-----|------------------------------------|--------------------|
| b   | without add-on blocks              | 85                 |
|     | with LAD 4BB                       | 98                 |
|     | with LA4 D●2                       | 114 <sup>(1)</sup> |
|     | with LA4 DF, DT                    | 123 <sup>(1)</sup> |
|     | with LA4 DW, DL                    | 130 <sup>(1)</sup> |
| c   | without cover or add-on blocks     | 90                 |
|     | with cover, without add-on blocks  | 92                 |
| c1  | with LAD N or C (2 or 4 contacts)  | 123                |
| c2  | with LA6 DK10, LAD 6K10            | 135                |
| c3  | with LAD T, R, S                   | 143                |
|     | with LAD T, R, S and sealing cover | 147                |
| (1) | Including LAD 4BB.                 |                    |

Connections and Schema

Wiring

---

