

Product data sheet

Specifications



TeSys LE - enclosed DOL starter - 50 A - 380 V AC coil - no pushbuttons

LE1D50AQ7A04

⚠ Discontinued on: Jun 27, 2020

⚠ Discontinued

Main

Range	TeSys
Product Name	TeSys LE
Device Short Name	LE1D
Product Or Component Type	Enclosed DOL starter
Device Application	Standard
Utilisation Category	AC-3
Device Composition	Thermal overload relay ordered separately Contactor
Control Type	Without

Complementary

Motor Power Kw	15 kW at 220/230 V AC 50/60 Hz 22 kW at 380/400 V AC 50/60 Hz 25 kW at 415 V AC 50/60 Hz 30 kW at 440 V AC 50/60 Hz 30 kW at 500 V AC 50/60 Hz 33 kW at 660/690 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	50 A
[Uc] Control Circuit Voltage	380 V AC 50/60 Hz
Cable Entry Number	1 ISO32 top 3 1 ISO20 + 2 ISO32 bottom
Width	200 mm
Height	300 mm
Depth	150 mm
Net Weight	4.85 kg

Environment

Material	Sheet steel
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient Air Temperature For Operation	-5...40 °C

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1