

# Product data sheet

Specifications



## Motion controller LMC212 12 axis - Acc kit - Basic

LMC212CAA10000

### Main

Range Of Product	PacDrive 3
Product Or Component Type	Motion controller

### Complementary

Product Compatibility	LMC212
Number Of Axis	12
Discrete Input Number	8 for digital input conforming to IEC 61131-2 Type 1 4 for touch probe input conforming to IEC 61131-2 Type 1
Discrete Input Voltage	- 3...5 V 15...30 V
Discrete Input Voltage Type	DC
Discrete Input Current	4 mA for digital input
Anti Bounce Filtering	100 µs...4.29 s configurable digital input 100 µs...4.29 s configurable touch probe input 100 µs...4.29 s configurable interrupt input
Maximum Cable Distance Between Devices	<50 m
Discrete Output Number	8 digital output
Discrete Output Current	500 mA for digital output
Maximum Leakage Current	0.5 mA
Maximum Number Of I/O Expansion Module	1
[Us] Rated Supply Voltage	24 V DC
Power Consumption In W	30 W
Memory Type	512 MB RAM DDR2 128 kB NVRAM
Programming Language	ST (structured text) IL (instruction list) LD (ladder) FBD (function block diagram) CFC (continuous function chart) SFC (sequential function chart)
Integrated Connection Type	2 Ethernet port, connector RJ45 for protocol Sercos 1 Ethernet port, connector RJ45 for protocol Ethernet 10/100BASE-T, FTP/HTTP 1 Ethernet port, connector RJ45 for master encoder 1 serial link, connector RJ45 for protocol RS232/RS485 1 CAN port, connector SUB-D 9 for protocol CANopen 1 USB port, connector USB type A
Supply	Power supply: 24 VDC
Width	44 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	270 mm
Depth	222 mm
Net Weight	2.2 kg

## Environment

Standards	CSA C22.2 No 142 CSA C22.2 No 14 UL 508 EN/IEC 61131-2
Product Certifications	CE EAC cULus CSA
Ambient Air Temperature For Operation	5...55 °C
Relative Humidity	5...95 % without condensation
Ip Degree Of Protection	IP20 conforming to EN/IEC 60529
Pollution Degree	2 conforming to IEC 61131-2
Operating Altitude	0...2000 m
Vibration Resistance	3.5 mm at 5...8.4 Hz 10 m/s² at 8.4...150 Hz
Shock Resistance	150 m/s² for 6 ms (operation) conforming to EN/IEC 60721-3-3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	32.5 cm
Package 1 Length	42.5 cm
Package 1 Weight	2.2 kg
Unit Type Of Package 2	S06
Number Of Units In Package 2	10
Package 2 Height	75.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	6.0 kg

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>