

Product data sheet

Specifications



TeSys K contactor , 3P ,AC-3, <= 440V, 12A , 1 NO aux , 60V DC coil

LP1K1210ND3

❗ Discontinued

Main

Range Of Product	TeSys K
Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LP1K
Utilisation Category	AC-3 AC-1 AC-4
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Poles Description	3P
Pole Contact Composition	3 NO
[Ie] Rated Operational Current	20 A (at <50 °C) at <= 440 V AC AC-1 for power circuit 12 A at <= 440 V AC AC-3 for power circuit 16 A (at <70 °C) at 690 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	type instantaneous 1 NO

Complementary

Contactor Application	Motor control Resistive load
Auxiliary Contact Composition	1 NO
Control Circuit Voltage Limits	Operational: 0.8...1.15 Uc (at <50 °C) Drop-out: 0.1...0.75 Uc (at <50 °C)
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to UL 508 Power circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-5-1 Signalling circuit: 600 V conforming to UL 508 Power circuit: 600 V conforming to CSA C22.2 No 14 Signalling circuit: 600 V conforming to CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
Mounting Support	Rail Plate
Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-50...80 °C
Operating Altitude	2000 m without derating
Tightening Torque	1.3 N.m - on screw clamp terminals - with screwdriver Philips No 2 1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
[Ue] Rated Operational Voltage	Power circuit: 690 V AC 50/60 Hz Signalling circuit: <= 690 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	20 A (at 50 °C) for power circuit 10 A (at 50 °C) for signalling circuit
Irms Rated Making Capacity	110 A AC for signalling circuit conforming to IEC 60947 144 A AC for power circuit conforming to NF C 63-110 144 A AC for power circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
Associated Fuse Rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
Operating Time	30...40 ms coil energisation and NO closing 10 ms coil de-energisation and NO opening
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	10 Mcycles
Maximum Operating Rate	3600 cyc/h
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.225 kg
Compatibility Code	LP1K

Environment

Inrush Power In W	3 W (at 20 °C)
Hold-In Power Consumption In W	3 W at 20 °C
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------