

# Product data sheet

Specifications



## EasyPact TVS contactor 3P(3 NO) - AC-3 - <= 440 V 25A - 220 V AC coil

LC1E2510M5

### Main

Range	EasyPact
Product name	EasyPact TVS
Product or component type	Contacteur
Device short name	LC1E
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	Power circuit: <= 690 V AC 50/60 Hz
[Ie] rated operational current	25 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 36 A (at <60 °C) at <= 440 V AC AC-1 for power circuit
Motor power kW	5.5 kW at 220...230 V AC 50/60 Hz 11 kW at 380...400 V 11 kW at 415 V 11 kW at 440 V 15 kW at 500 V 15 kW at 660...690 V
Control circuit type	AC at 50 Hz
[Uc] control circuit voltage	220 V AC 50 Hz
Height	74 mm
Width	45 mm
Depth	85 mm
Net weight	0.36 kg
Colour	Grey (RAL 7011)

### Complementary

Auxiliary contact composition	1 NO
[Uimp] rated impulse withstand voltage	6 kV coil not connected to the power circuit conforming to IEC 60947
[Ui] rated insulation voltage	690 V conforming to IEC 60947-4-1
Overvoltage category	III
Irms rated making capacity	250 A at 440 V AC for power circuit conforming to IEC 60947-4-1

<b>Rated breaking capacity</b>	200 A at 440 V for power circuit conforming to IEC 60947
<b>[Icw] rated short-time withstand current</b>	240 A 40 °C - 10 s for power circuit 120 A 40 °C - 60 s for power circuit 50 A 40 °C - 600 s for power circuit
<b>Associated fuse rating</b>	10 A gG at ≤ 690 V coordination type 1 for control circuit conforming to IEC 60947-5-1 40 A gG at ≤ 690 V coordination type 1 for power circuit
<b>Average impedance</b>	2.5 mOhm - Ith 36 A 50 Hz for power circuit
<b>Power dissipation per pole</b>	1.6 W AC-3 3.2 W AC-1
<b>Control circuit voltage limits</b>	Operational: 0.85...1.1 Uc at 50 Hz (at <55 °C) Drop-out: 0.3...0.6 Uc at 50 Hz (at <55 °C)
<b>Operating time</b>	12...22 ms on closing 4...19 ms on opening
<b>Mechanical durability</b>	10000000 cycles
<b>Maximum operating rate</b>	1800 cyc/h 60 °C
<b>Inrush power in VA</b>	95 VA 50 Hz cos phi 0.75 (at 20 °C) 95 VA 60 Hz cos phi 0.75 (at 20 °C)
<b>Hold-in power consumption in VA</b>	8.3 VA 50 Hz cos phi 0.3 (at 20 °C) 8.5 VA 60 Hz cos phi 0.3 (at 20 °C)
<b>Heat dissipation</b>	2...3 W for control circuit
<b>Minimum switching current</b>	5 mA for control circuit
<b>Minimum switching voltage</b>	17 V for control circuit
<b>Non-overlap time</b>	1.5 ms on energisation guaranteed between NC and NO contact 1.5 ms on de-energisation guaranteed between NC and NO contact
<b>Insulation resistance</b>	> 10 MOhm for control circuit
<b>Electrical durability</b>	350000 cycles AC-1 300000 cycles AC-3
<b>Mounting support</b>	Plate DIN rail
<b>Connections - terminals</b>	Control circuit: screw clamp terminals 1 1...4 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...4 mm <sup>2</sup> - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm <sup>2</sup> - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...4 mm <sup>2</sup> - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...4 mm <sup>2</sup> - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 1.5...6 mm <sup>2</sup> - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 1.5...6 mm <sup>2</sup> - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 1...6 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 1...4 mm <sup>2</sup> - cable stiffness: flexible with cable end
<b>Recommended tightening torque</b>	Control circuit: 1.2 N.m Power circuit: 1.5 N.m
<b>Max tightening torque</b>	Control circuit: 1.4 N.m Power circuit: 1.7 N.m

## Environment

<b>Standards</b>	IEC 60947-1 IEC 60947-4-1 IEC 60947-5-1
<b>Product certifications</b>	EAC CE
<b>IP degree of protection</b>	IP2x conforming to IEC 60529
<b>Protective treatment</b>	TH (pollution degree 3) conforming to IEC 60068-2-30 test Db
<b>Pollution degree</b>	3
<b>Ambient air temperature for operation</b>	-5...55 °C
<b>Ambient air temperature for storage</b>	-60...80 °C

Permissible ambient air temperature around the device	-20...70 °C at Uc
Operating altitude	3000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-1
Mechanical robustness	Vibrations contactor open: 1.5 Gn, 5...300 Hz Vibrations contactor closed: 3 Gn, 5...300 Hz Shocks contactor closed: 10 Gn for 11 ms Shocks contactor open: 6 Gn for 11 ms

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	356 g
Package 1 Height	8.7 cm
Package 1 width	5 cm
Package 1 Length	7.6 cm
Unit Type of Package 2	S02
Number of Units in Package 2	36
Package 2 Weight	13.295 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P06
Number of Units in Package 3	576
Package 3 Weight	220.836 kg
Package 3 Height	77 cm
Package 3 width	80 cm
Package 3 Length	60 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------