

# Product data sheet

Specifications



circuit breaker ComPact NSXm B  
(25 kA at 415 VAC), 3P 3d, 80 A  
rating TMD trip unit, EverLink  
connectors

LV426206

⚠ Discontinued on: Oct 26, 2023

⚠ Discontinued

Important message: This product has been switched to new  
ComPacT range and is no longer commercialized.

## Main

Range	ComPact
Product Name	ComPact NSXm
Range Of Product	ComPact NSXm
Device Short Name	NSXm 80B
Product Or Component Type	Circuit breaker
Device Application	Distribution Protection
Number Of Poles	3P
Protected Poles Description	3D
[In] Rated Current	80 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	50 kA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	B 25 kA 415 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	LI
Control Type	Toggle
Circuit Breaker Mounting Mode	By screws Clip-on

## Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>[Ics] Rated Service Short-Circuit Breaking Capacity</b>	50 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
<b>Mechanical Durability</b>	20000 cycles
<b>Electrical Durability</b>	10000 cycles at 440 V In 20000 cycles at 440 V In/2 5000 cycles at 690 V In 10000 cycles at 690 V In/2
<b>Mounting Support</b>	Plate DIN rail
<b>Connection Terminals</b>	1 Everlink lug wire size 2.5...95 mm², rigid or stranded aluminium/copper 1 Everlink lug wire size 2.5...70 mm², flexible copper
<b>Connection Pitch</b>	35 mm with spreaders 27 mm without spreaders
<b>9 Mm Pitches</b>	9 module
<b>Protection Type</b>	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
<b>Trip Unit Rating</b>	80 A at 40 °C
<b>Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)</b>	Adjustable
<b>[Ir] Long-Time Protection Pick-Up Adjustment Range</b>	0.7...1 x In
<b>Long-Time Protection Delay Adjustment Type Tr</b>	Fixed
<b>[Im] Magnetic Protection Pick-Up Range</b>	1000 A
<b>Earth-Leakage Protection</b>	Without
<b>Number Of Slots For Electrical Auxiliaries</b>	1 slot(s) for auxiliary switch OF 1 slot(s) for alarm switch SD 1 slot(s) for voltage release MN or MX
<b>Width (W)</b>	81 mm
<b>Height (H)</b>	137 mm
<b>Depth (D)</b>	80 mm
<b>Net Weight</b>	1.06 kg
<b>Colour</b>	Grey (RAL 7016)

## Environment

<b>Standards</b>	EN/IEC 60947
<b>Product Certifications</b>	CCC EAC Marine
<b>Pollution Degree</b>	3 conforming to IEC 60664-1
<b>Ip Degree Of Protection</b>	IP40 conforming to IEC 60529
<b>Ik Degree Of Protection</b>	IK07 conforming to IEC 62262
<b>Ambient Air Temperature For Operation</b>	-25...70 °C
<b>Ambient Air Temperature For Storage</b>	-50...85 °C
<b>Relative Humidity</b>	0...95 %
<b>Operating Altitude</b>	0...2000 m without derating 2000...5000 m with derating

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	12.5 cm
Package 1 Length	22 cm
Package 1 Weight	1.3 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	9
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	12.29 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	72
Package 3 Height	50 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	110.32 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>