

Product data sheet

Specifications



TeSys F contactor - 3P (3 NO) - AC-1 - <= 1000 V 1700 A - coil 250 V DC

LC1F1700UD

ⓘ Discontinued

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactors
Device Short Name	LC1F
Contactors Application	Resistive load
Utilisation Category	AC-1
Poles Description	3P
[Ue] Rated Operational Voltage	<= 1000 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	250 V DC
[Ie] Rated Operational Current	1700 A (at <40 °C) AC AC-1

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	1700 A (at 40 °C)
Rated Breaking Capacity	2550 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	10000 A 40 °C - 10 s 7500 A 40 °C - 30 s 5500 A 40 °C - 1 min 4200 A 40 °C - 3 min 3000 A 40 °C - 10 min
Associated Fuse Rating	1600 A gG at <= 440 V
Average Impedance	0.1 mOhm - Ith 1700 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C 1000 V conforming to UL 60947-4-1
Power Dissipation Per Pole	200 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	3 NO
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.2...0.35 Uc (at 55 °C)
Inrush Power In W	2100 W (at 20 °C)
Hold-In Power Consumption In W	10 W at 20 °C
Maximum Operating Rate	600 cyc/h 55 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Time	50...60 ms closing 45...60 ms opening
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²solid without cable end Power circuit: bar 3 cable(s) - busbar cross section: 100 x 5 mm Power circuit: bolted connection
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 58 N.m
Mounting Support	Plate
Heat Dissipation	10 W
Standards	EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 JIS C8201-4-1 EN 60947-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product Certifications	UL CSA CCC CB Scheme EAC
Compatibility Code	LC1F
Control Circuit Type	DC standard

Environment

Protective Treatment	TH
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-60...80 °C
Permissible Ambient Air Temperature Around The Device	-40...60 °C
Height	332 mm
Width	438 mm
Depth	238.6 mm
Operating Altitude	3000 m without derating
Net Weight	30 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)