

# Product data sheet

Specifications



contactor, TeSys F, 3P(3NO), AC1,  
<=1000V AC 2600 A, coil 220V DC

LC1F2600MD

## Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	3P
[Ue] Rated Operational Voltage	<= 1000 V AC 50/60 Hz
[Uc] Control Circuit Voltage	220 V DC
[Ie] Rated Operational Current	2600 A (at <60 °C) AC AC-1

## Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	2600 A (at 60 °C)
Rated Breaking Capacity	3900 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	12000 A 40 °C - 10 s 9000 A 40 °C - 30 s 7000 A 40 °C - 1 min 6000 A 40 °C - 3 min 4000 A 40 °C - 10 min
Associated Fuse Rating	2500 A gG at <= 440 V
Average Impedance	0.1 mOhm - Ith 2600 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1 1000 V conforming to UL 60947-4-1
Power Dissipation Per Pole	250 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	3 NO
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.2...0.35 Uc (at 55 °C)
Inrush Power In W	2600 W (at 20 °C)
Hold-In Power Consumption In W	18 W at 20 °C
Maximum Operating Rate	600 cyc/h 55 °C
Operating Time	60...70 ms closing 40...50 ms opening

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm²solid without cable end Power circuit: bar 3 cable(s) - busbar cross section: 100 x 10 mm
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 58 N.m
Mounting Support	Plate
Heat Dissipation	40 W
Standards	EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 EN 60947-1 JIS C8201-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product Certifications	CB Scheme CCC CSA UL UKCA EAC
Compatibility Code	LC1F
Control Circuit Type	DC standard

## Environment

Ip Degree Of Protection	IP20 front face with shrouds conforming to IEC 60529 IP20 front face with shrouds conforming to VDE 0106
Protective Treatment	TH
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-60...80 °C
Permissible Ambient Air Temperature Around The Device	-40...60 °C
Height	382 mm
Width	519 mm
Depth	251 mm
Operating Altitude	3000 m without derating
Net Weight	36 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	38.0 cm
Package 1 Width	50.0 cm
Package 1 Length	60.0 cm
Package 1 Weight	37.0 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)