

Product data sheet

Specifications



Circuit breaker, ComPact NSX160F, 36kA/415VAC, MicroLogic 4.2AB Vigi trip unit, 160A, 4 poles 4d

LV433857

⚠ Discontinued on: Sep 21, 2023

⚠ Discontinued

Important message: This product has been switched to new ComPacT range and is no longer commercialized.

Main

Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100...250
Device Short Name	VigiCompact NSX160F
Product Or Component Type	Earth leakage circuit breaker
Device Application	Special application
Number Of Poles	4P
Protected Poles Description	3t + N/2 3t 4t
Neutral Position	Left
[In] Rated Current	160 A at 40 °C
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	F 36 kA 415 V AC
Trip Unit Name	MicroLogic 4.2 AB
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LSolR
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ics] Rated Service Short-Circuit Breaking Capacity	85 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 36 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	40000 cycles
Electrical Durability	20000 cycles at 440 V In 40000 cycles at 440 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection R : for earth-leakage protection
Trip Unit Rating	160 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	90...160 A
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	11 s at 7.2 x Ir 16 s at 6 x Ir 400 s at 1.5 x Ir
Thermal Memory	20 minutes before and after tripping
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable
[Isd] Short-Time Protection Pick-Up Adjustment Range	1.5...10 x Ir
Short-Time Protection Delay Adjustment Type Tsd	Fixed
[Tsd] Short-Time Protection Delay Adjustment Range	0.02 s
Instantaneous Protection Pick-Up Adjustment Type Ii	Fixed
[Ii] Instantaneous Protection Pick-Up Adjustment Range	1600 A
Earth-Leakage Protection	Integrated
Earth-Leakage Protection Class	Class A
Earth-Leakage Protection Sensitivity Adjustment Type IΔn	Adjustable
[IΔn] Earth-Leakage Protection Sensitivity Adjustment Range	30 mA 100 mA 300 mA 500 mA 1 A 3 A 5 A
Earth-Leakage Protection Specific Mode	OFF using the IΔn rotary switch
Earth-Leakage Protection Time Delay Adjustment Type Δt	Adjustable
[Δt] Earth-Leakage Protection Time Delay Adjustment Range	0 ms 60 ms 150 ms 500 ms 1 s
Neutral Protection Settings	0.5 x Ir (3t + N/2) 1 x Ir (4t) No protection (3t)
Zone Selective Interlocking Zsi	Without

Number Of Slots For Electrical Auxiliaries	5 slot(s)
Local Signalling	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload
Width (W)	140 mm
Height (H)	161 mm
Depth (D)	86 mm
Net Weight	2.4 kg

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.6 cm
Package 1 Width	14.3 cm
Package 1 Length	19.2 cm
Package 1 Weight	2.628 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	10.8 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov