

Product data sheet

Specifications



Circuit breaker basic frame, ComPact NSX250S DC, 100kA at 750VDC, 250A, without trip unit, 4 poles

LV438219

! Discontinued

! Discontinued on: Oct 26, 2023

Important message: This product has been switched to new ComPacT range and is no longer commercialized.

Main

Range	ComPact
Range Of Product	ComPact NSX100...250 DC
Device Short Name	NSX250S DC
Product Or Component Type	Basic frame
Device Application	Distribution
Circuit Breaker Name	Compact NSX250S DC
Number Of Poles	4P
[In] Rated Current	250 A at 40 °C
[Ue] Rated Operational Voltage	750 V DC
Network Type	DC
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	100 kA Icu at 250 V DC 1P conforming to IEC 60947-2 100 kA Icu at 24...125 V DC 1P conforming to IEC 60947-2 100 kA Icu at 500 V DC 2P conforming to IEC 60947-2 100 kA Icu at 750 V DC 3P conforming to IEC 60947-2
Performance Level	S 100 kA 750 V DC
Control Type	Toggle
Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	750 V DC conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	100 kA at 250 V DC conforming to IEC 60947-2 (1P) 100 kA at 48/125 V DC conforming to IEC 60947-2 (1P) 100 kA at 500 V DC conforming to IEC 60947-2 (2P) 100 kA at 750 V DC conforming to IEC 60947-2 (3P)
Maximum Breaking Time	10 ms
Mechanical Durability	10000 cycles conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Durability	10000 cycles 250 V DC In/2 conforming to IEC 60947-2 10000 cycles 500 V DC In/2 conforming to IEC 60947-2 10000 cycles 750 V DC In/2 conforming to IEC 60947-2 5000 cycles 250 V DC In conforming to IEC 60947-2 5000 cycles 500 V DC In conforming to IEC 60947-2 5000 cycles 750 V DC In conforming to IEC 60947-2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	Without protection
Width (W)	140 mm
Height (H)	161 mm
Depth (D)	86 mm

Environment

Standards	IEC 60947-2
Product Certifications	LCIE KEMA ASTA ASEFA
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	14.3 cm
Package 1 Length	18.8 cm
Package 1 Weight	2.165 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.038 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov