

# Product data sheet

Specifications



## Circuit breaker frame, MasterPact MTZ1 06H3 fixed for MicroLogic X, 630A, 66kA/415VAC (Icu), 4P

LV846443

### Main

Range	MasterPacT
Product Name	MasterPact MTZ1
Device Short Name	MTZ1 06 H3
Product Or Component Type	Circuit breaker
Device Application	Power distribution protection
Poles Description	4P
Neutral Position	Left
Control Unit	Without control unit
Product Compatibility	control unit MicroLogic 2.0 X control unit MicroLogic 5.0 X control unit MicroLogic 6.0 X control unit MicroLogic 7.0 X control unit MicroLogic 2.0 Xi control unit MicroLogic 5.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 7.0 Xi
[In] Rated Current	630 A at 40 °C
Performance Type	H3 66 kA 415 V AC
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Selectivity Category	Category B
Control Type	Push-button
Mounting Mode	Fixed

### Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	66 kA at 220/415 V AC 50/60 Hz 66 kA at 440 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	50 kA at 440 V AC 50/60 Hz 50 kA at 220/415 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	30 kA 3 s 50 kA 1 s 50 kA 0.5 s
[Icm] Rated Short-Circuit Making Capacity	145 kA 220/415 V AC at 50/60 Hz 145 kA 440 V AC at 50/60 Hz
Integrated Instantaneous Protection (Din In Ka Peak)	99...121 kA
Sensor Rating	400 A 630 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	30 W
Maximum Breaking Time	25 ms
Maximum Closing Response Time	50 ms
Mounting Support	Rails Base plate
Upside Connection	Front Rear
Downside Connection	Front Rear
Connection Pitch	70 mm
Mechanical Durability	10000 cycles with periodic preventive maintenance
Electrical Durability	6000 cycles 440 V AC 50/60 Hz at In conforming to EN/IEC 60947-2 AC-23A: 6000 cycles 440 V AC 50/60 Hz at In conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440 V AC 50/60 Hz at In conforming to EN/IEC 60947-3
Height	301 mm
Width	346 mm
Depth	209 mm
Net Weight	18 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-2 Annex H IEC 61557-12
Product Certifications	CE IECEE CB Scheme

## Environment

Ip Degree Of Protection	IP30 conforming to EN 60529
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	0...2000 m without derating 2000...5000 m with derating

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.0 cm
Package 1 Width	30.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	15.0 kg

# Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>