

# Product data sheet

Specifications



## Anti Harmonic PowerLogic PFC detuned reactor, 12.5kvar 190Hz (3.8) 7% 50Hz 690V

LVR07125A69T

⚠ To be discontinued on: Sep 30, 2024

⚠ To be discontinued

### Main

Range	PowerLogic
Device Short Name	DR
Product Or Component Type	Detuned reactor
Network Frequency	50 Hz
Reactive Power Rating	12.5 kvar for 690 V AC 50 Hz
Network Rated Voltage	690 V AC 50 Hz
Tuning Order	3.8 - 190 Hz - 7 % - 50 Hz

### Complementary

Power Losses (Max)	150 W
Value Of Inductance	8.893 mH
Inductance Tolerance	- 5 % to 5 % per phase
Fundamental Current Rating	10.5 A
Rms Current Rating	11.3 A
Electrical Insulation Class	Class H
[Ui] Rated Insulation Voltage	1.1 kV
Dielectric Test Voltage	4 kV 50 Hz 1 minute
[Imp] Maximum Permanent Current	1.2 x I1
Harmonic Current Spectrum	3.7 % x I3 38.2 % x I5 13.6 % x I7 4.9 % x I11
Dynamic Withstand Current	2.2 x Isc
[Ith] Conventional Free Air Thermal Current	2 A at 250 V AC 50 Hz
Type Of Installation	Indoor installation
Type Of Cooling	Forced convection
Connections - Terminals	Pad terminal
Fixing Center	200 x 125 mm
Height	220 mm
Width	240 mm
Depth	160 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	12.5 kg
------------	---------

## Environment

Standards	IEC 60068
Ip Degree Of Protection	IP00
Operating Altitude	<= 2000 m
Ambient Air Temperature For Operation	0...55 °C at <= 1000 m 0...50 °C at > 1000...2000 m
Average Ambient Air Temperature For Operation	50 °C at <= 1000 m (average over 24 hours) 40 °C at <= 1000 m (average over 1 year) 45 °C at > 1000...2000 m (average over 24 hours) 35 °C at > 1000...2000 m (average over 1 year)
Climatic Withstand	Relative humidity: 20...80 % Salt mist (400 V/50 Hz) : 250 hours

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.000 cm
Package 1 Width	30.000 cm
Package 1 Length	30.000 cm
Package 1 Weight	12.500 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	4
Package 2 Height	75.000 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	60.600 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations