

# Product data sheet

Specifications



ION8650 meter 32MB, 9S/29S/36S,  
277VAC/300VDC 50Hz, standard  
3I+4O, password

M8650C0C0J5A0B1A

⚠ Discontinued on: Jul 21, 2023

⚠ Discontinued

## Main

Range	PowerLogic
Device Short Name	ION8650C
Product Or Component Type	Revenue and power quality meter

## Complementary

Power Quality Analysis	up to the 31st harmonic harmonic distortion voltage sag and swell detection programmability (logic and math functions)
Device Application	Tariff metering Equipment monitoring and control Demand and power factor control Co-generation and IPP monitoring Instrument transformer correction Energy pulsing and totalisation Load curtailment
Type Of Measurement	Current Voltage Frequency Apparent power total Power factor total Apparent power per phase Power factor per phase Active power total Active power per phase Reactive power total Reactive power per phase
Supply Voltage	120...277 V AC 47...63 Hz 160...277 V AC 47...63 Hz 200...300 V DC
Network Frequency	50 Hz
Outlet Standard	American
[In] Rated Current	2 A 5 A 1 A
Type Of Network	3P + N 1P + N 3P
Power Consumption In Va	24 VA
Maximum Power Consumption In Va	33 VA
Display Type	FSTN transreflective LCD

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Form Designation	9S 3-element 4 36S 2½-element 4 29S 2½-element 4
Sampling Rate	1024 samples/cycle
Measurement Current	0.001...24 A
Input Type	Current 0.01...20 A (impedance 0.05 Ohm)
Measurement Voltage	57...277 V AC phase to neutral 100...480 V AC phase to phase
Number Of Inputs	3 digital 0.001...100 mA 30 V DC
Measurement Accuracy	Current 0.1 % Voltage 0.1 % Power 0.1 % Power factor 0.1 % Frequency 0.001 Hz Energy 0.1 %
Accuracy Class	Class 0.2S energy conforming to IEC 62053-23 Class 0.2 energy conforming to ANSI C12.20 Class 0.2S energy conforming to IEC 62053-22
Number Of Outputs	2 pulse 4 form C relay output
Communication Port Protocol	DNP3 at 300...115200 bauds ION at 300...115200 bauds Ansi C12.18 at <= 19200 bauds DLMS at 300...115200 bauds Modbus at 57600 bauds Modbus RTU, slave at 300...115200 bauds
Communication Port Support	SUB-D 9: RS485/RS232 Terminal block: RS485 Infrared
Time Synchronisation Protocol	IRIG-B GPS: Truetime/Datum
Data Recording	Alarms Revenue logs Time stamping GPS synchronisation Event logs Sag and swell logs Historical logs Harmonics logs Data logs
Transmission Rate	57600 bauds <= 19200 bauds 300...115200 bauds
Memory Capacity	32 MB
Web Services	Alarm notification by e-mail Web server Port addressing user designed Robust security logs
Ethernet Service	SNMP-Traps and SYSLOG Enable/disable Ethernet protocols Enable/disable serial ports
Tamperproof Of Settings	Hardware lock by jumper Protected by access code
Compatibility Code	ION8650C

## Environment

Electromagnetic Compatibility	Electrostatic discharge immunity test conforming to IEC 61000-4-2 Conducted RF disturbances conforming to IEC 61000-4-6 Immunity to impulse waves conforming to IEC 61000-4-12 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Susceptibility to electromagnetic fields conforming to IEC 61000-4-3 1.2/50 µs shock waves immunity test conforming to IEC 61000-4-5 Conducted and radiated emissions B conforming to CISPR 22
Mounting Mode	Socket-mounted
Mounting Support	Enclosure door
Type Of Installation	Indoor installation
Overvoltage Category	III
Ip Degree Of Protection	IP65 front face: IP51 back:
Relative Humidity	5...95 %
Pollution Degree	2
Ambient Air Temperature For Operation	-40...85 °C
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	0...3000 m
Standards	ANSI C12.1 IEC 62052-11
Width	178 mm
Depth	237 mm
Height	178 mm
Net Weight	7 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26.0 cm
Package 1 Width	28.0 cm
Package 1 Length	44.0 cm
Package 1 Weight	4.5 kg

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a>
Environmental Disclosure		<a href="#">Product Environmental Profile</a>
Circularity Profile		<a href="#">End of Life Information</a>
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	