

Product data sheet

Specifications



Miniature circuit breaker (MCB), Multi9 C60N, 4P, 20A, C curve, 10kA (IEC/EN 60947-2)

M9F11420

Main

Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60N
Device Application	Distribution
Poles Description	4P
Number Of Protected Poles	4
[In] Rated Current	20 A at 50 °C conforming to EN/IEC 60947-2
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	40 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2 10 kA Icu at 415 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2 20 kA Icu at 240 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2 6 kA Icu at 440 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2
Utilisation Category	Category A conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Standards	EN/IEC 60947-2
Product Certifications	EAC CCC

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz between phases 415 V AC 50/60 Hz between phases 440 V AC 50/60 Hz between phases <= 250 V DC
Magnetic Tripping Limit	8.5 x In +/- 20 % AC 12 x In +/- 20 % DC
[Ics] Rated Service Breaking Capacity	7.5 kA 75 % conforming to EN/IEC 60947-2 - 415 V AC 50/60 Hz 16 kA 75 % conforming to EN/IEC 60947-2 - 240 V AC 50/60 Hz 4.5 kA 75 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 40 kA 100 % conforming to EN/IEC 60947-2 - <= 250 V DC
Limitation Class	3
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	8
Height	81 mm
Width	72 mm
Depth	72 mm
Net Weight	0.48 kg
Colour	Grey
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Tunnel type terminal (top or bottom)1...25 mm² - rigid Tunnel type terminal (top or bottom)1...25 mm² - flexible Tunnel type terminal (top or bottom)1...25 mm² - flexible with ferrule
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Separate block

Environment

Heat Dissipation	12 W at 415 V - 20 A
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	7.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	424.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	8.0 cm

Package 2 Width	8.8 cm
Package 2 Length	22.0 cm
Package 2 Weight	1.315 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	16.318 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations