

Product data sheet

Specifications



TeSys LE - enclosed star-delta starter - 35 A - 400 V AC coil- no pushbuttons

LE3D35V7A04

⚠ Discontinued on: Jun 27, 2020

⚠ Discontinued

Main

Range	TeSys
Product Name	TeSys LE
Device Short Name	LE3D
Product Or Component Type	Enclosed star-delta starter
Device Application	Standard
Material	Polycarbonate
Utilisation Category	AC-3
Device Composition	Thermal overload relay ordered separately Star-delta contactors Mechanical interlock
[Ie] Rated Operational Current	35 A AC-3
Motor Power Kw	15 kW at 220 V AC 50/60 Hz 30 kW at 380/400 V AC 50/60 Hz 30 kW at 415 V AC 50/60 Hz 30 kW at 440 V AC 50/60 Hz
[Uc] Control Circuit Voltage	400 V AC 50/60 Hz
Control Type	Without

Complementary

Connections - Terminals	Power circuit: screw clamp terminals Control circuit: screw clamp terminals
Cable Entry Number	2 ISO20 top 2 ISO25 top 2 ISO32 top 2 ISO40 top 2 ISO20 bottom 2 ISO25 bottom 2 ISO32 bottom 2 ISO40 bottom
Width	186 mm
Height	348 mm
Depth	167 mm
Net Weight	5.16 kg

Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60947-4-1
Ambient Air Temperature For Operation	-5...40 °C
Environmental Characteristic	Standard environment

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration

China Rohs Regulation	China RoHS declaration
-----------------------	--

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---