

Product data sheet

Specifications



TeSys LE - enclosed DOL starter - 25 A - 120 V AC coil

LE4D25G7

! Discontinued

Main

Range	TeSys
Product Name	TeSys LE
Device Short Name	LE4D
Product Or Component Type	Enclosed DOL starter
Device Application	Standard
Material	Polycarbonate
Utilisation Category	AC-3
Device Composition	Thermal overload relay ordered separately Contactor Fuse disconnecter
Motor Power Kw	11 kW at 380/400 V AC 50/60 Hz 11 kW at 415 V AC 50/60 Hz 11 kW at 440 V AC 50/60 Hz 15 kW at 500 V AC 50/60 Hz 5.5 kW at 220/230 V AC 50/60 Hz
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	25 A
Associated Fuse Rating	25 A 10 x 38 mm aM
Control Type	Push-button start green I Push-button stop/reset red O

Complementary

Cable Entry Number	2 ISO20 top 2 ISO25 top 2 ISO32 top 2 ISO40 top 2 ISO20 bottom 2 ISO25 bottom 2 ISO32 bottom 2 ISO40 bottom
Width	186 mm
Height	330 mm
Depth	175.5 mm
Net Weight	2.2 kg

Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529
-------------------------	------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient Air Temperature For Operation	-5...40 °C
Environmental Characteristic	Standard environment

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26 cm
Package 1 Width	29 cm
Package 1 Length	46 cm
Package 1 Weight	3.201 kg