

# Product data sheet

Specifications



surge arrester, Multi9 PRD1 75r, 4P,  
120/240 V

M9L17240

## Main

Range	Multi9
Product Name	Multi9 PRD1
Product Or Component Type	Surge arrester
Device Short Name	PRD1 75r
Poles Description	4P
Remote Signalling	With
Signal Contacts Composition	1 SD (1 C/O)
Surge Arrester Type	Electrical distribution network

## Complementary

Surge Arrester Class Type	Type 1
Surge Arrester Technology	MOV
Wiring Configuration	5-wire
Nominal Discharge Current	Common mode: 20 kA (L/PE)
Maximum Discharge Current	75 kA
[Iimp] Impulse Current	75 kA
[Uc] Maximum Continuous Operating Voltage	Common mode: 175 V AC L/N Differential mode: 350 V AC L/L Common mode: 350 V AC L/PE Common mode: 175 V AC N/PE Differential mode: 450 V AC H/L Common mode: 450 V AC H/PE Common mode: 275 V AC H/N
Maximum [Up] Voltage Protection Level	Common mode <1200 V L/PE Differential mode <600 V L/N Common mode <1200 V L/L Common mode <600 V N/PE Differential mode <1500 V H/L Common mode <1500 V H/PE Common mode <800 V H/N
Disconnecter Device Type	Associated circuit breaker 30 A curve C 14 kA
Short-Circuit Withstand	200 kA
Local Signalling	Green mechanical indicator for operating Red mechanical indicator for end of life
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	8
Height	91.7 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	70 mm
Depth	71.4 mm
Net Weight	703 g
Colour	Grey (RAL 7035)
Response Time	< 25 ns
Connections - Terminals	Tunnel type terminal6...35 mm² (AWG 10...AWG 2) - rigid Tunnel type terminal6...25 mm² (AWG 10...AWG 4) - flexible Tunnel type terminal (dry contacts)0.5...1.5 mm²
Wire Stripping Length	10 mm for L/N connection 10 mm for PE connection 6 mm for dry contacts connection
Tightening Torque	3 N.m L/N 3 N.m PE

## Environment

Standards	UL 1449:ed. 4
Ip Degree Of Protection	NEMA 1 built-in:
Pollution Degree	3
Relative Humidity	0...95 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	9.0 cm
Package 1 Length	12.0 cm
Package 1 Weight	515.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	12
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.505 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging

## Resource performance

✔ Sustainable Packaging

## Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information      Yes

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins