


Product data sheet

Specifications



TeSys K changeover contactor , 4P , AC,1 ≤ 440 V 20 A , 250 V DC coil

LP2K09004UD

ⓘ Discontinued

Main

| | |
|---|---|
| Range | TeSys |
| Product Name | TeSys K |
| Product Or Component Type | Changeover contactor |
| Device Short Name | LP2K |
| Device Application | Control |
| Contactor Application | Resistive load |
| Utilisation Category | AC-1 |
| Device Presentation | Preassembled with reversing power busbar |
| Poles Description | 4P |
| Power Pole Contact Composition | 4 NO |
| [Ue] Rated Operational Voltage | Power circuit: 690 V AC 50/60 Hz |
| [Ie] Rated Operational Current | 20 A (at <50 °C) at ≤ 440 V AC AC-1 for power circuit 16 A (at <70 °C) at 690 V AC AC-1 for power circuit |
| Control Circuit Type | DC standard |
| [Uc] Control Circuit Voltage | 250 V DC |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |
| Overvoltage Category | III |
| [Ith] Conventional Free Air Thermal Current | 20 A (at 50 °C) for power circuit |
| Irms Rated Making Capacity | 110 A AC for power circuit conforming to NF C 63-110 110 A AC for power circuit conforming to IEC 60947 |
| Rated Breaking Capacity | 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947 |
| [Icw] Rated Short-Time Withstand Current | 90 A 50 °C - 1 s for power circuit 85 A 50 °C - 5 s for power circuit 80 A 50 °C - 10 s for power circuit 60 A 50 °C - 30 s for power circuit 45 A 50 °C - 1 min for power circuit 40 A 50 °C - 3 min for power circuit 20 A 50 °C - ≥ 15 min for power circuit |
| Associated Fuse Rating | 25 A gG at ≤ 440 V for power circuit 25 A aM for power circuit |
| Average Impedance | 3 mOhm - Ith 20 A 50 Hz for power circuit |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------------|--|
| [Ui] Rated Insulation Voltage | Power circuit: 600 V conforming to UL 508 Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V conforming to CSA C22.2 No 14 |
| Electrical Durability | 0.18 Mcycles 20 A AC-1 at Ue <= 440 V |
| Interlocking Type | Mechanical |
| Mounting Support | Plate Rail |
| Standards | BS 5424 VDE 0660 NF C 63-110 IEC 60947 |
| Product Certifications | CB Scheme CCC UL CSA EAC CE UKCA |
| Connections - Terminals | Screw clamp terminals 1 cable(s) 1.5...4 mm²solid Screw clamp terminals 1 cable(s) 0.75...4 mm²flexible without cable end Screw clamp terminals 1 cable(s) 0.34...2.5 mm²flexible with cable end Screw clamp terminals 2 cable(s) 1.5...4 mm²solid Screw clamp terminals 2 cable(s) 0.75...4 mm²flexible without cable end Screw clamp terminals 2 cable(s) 0.34...1.5 mm²flexible with cable end |
| Tightening Torque | 1.3 N.m - on screw clamp terminals - with screwdriver Philips No 2 1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm |
| Operating Time | 30...40 ms coil energisation and NO closing 10 ms coil de-energisation and NO opening |
| Safety Reliability Level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical Durability | 5 Mcycles |
| Maximum Operating Rate | 3600 cyc/h |

Complementary

| | |
|--------------------------------|---|
| Control Circuit Voltage Limits | Operational: 0.8...1.15 Uc (at <50 °C) Drop-out: 0.1...0.75 Uc (at <50 °C) |
| Inrush Power In W | 3 W (at 20 °C) |
| Hold-In Power Consumption In W | 3 W at 20 °C |
| Heat Dissipation | 3 W |

Environment

| | |
|---------------------------------------|--|
| Ip Degree Of Protection | IP20 conforming to VDE 0106 |
| Protective Treatment | TC conforming to IEC 60068 TC conforming to DIN 50016 |
| Ambient Air Temperature For Operation | -25...50 °C |
| Ambient Air Temperature For Storage | -50...80 °C |
| Operating Altitude | 2000 m without derating |
| Flame Retardance | V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102 |

| | |
|-----------------------|---|
| Mechanical Robustness | Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6 Shocks contactor opened, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on X axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 |
| Height | 58 mm |
| Width | 90 mm |
| Depth | 57 mm |
| Net Weight | 0.48 kg |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|