

Product data sheet

Specifications



power meter PowerLogic PM5341,
ethernet, up to 31st Harmonic,
256KB 2DI/2DO 35 alarms, MID

METSEPM5341

Main

Range	PowerLogic
Product Name	PowerLogic PM5000
Device Short Name	PM5341
Product Or Component Type	Power meter

Complementary

Power Quality Analysis	up to the 31st harmonic
Device Application	Power monitoring Multi-tariff
Type Of Measurement	Current Voltage Frequency Power factor Energy Active and reactive power
Supply Voltage	90...450 V AC 45...65 Hz 100...300 V DC
Network Frequency	50 Hz 60 Hz
[In] Rated Current	5 A 1 A
Type Of Network	1P + N 3P + N 3P
Maximum Power Consumption In Va	11 VA at 415 V
Ride-Through Time	80 ms 120 V AC typical 100 ms 230 V AC typical 100 ms 415 V AC typical 50 ms 125 V DC typical
Display Type	Monochrome graphic LCD
Display Resolution	128 x 128 pixels
Sampling Rate	64 samples/cycle
Measurement Current	5...8500 mA
Analogue Input Type	Voltage (impedance 10 MOhm) Current (impedance <= 0.3 mOhm)
Measurement Voltage	35...760 V AC 45...65 Hz between phases 20...400 V AC 45...65 Hz between phase and neutral
Frequency Measurement Range	45...65 Hz
Number Of Inputs	2 digital

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Measurement Accuracy	Active energy +/- 0.5 % Reactive energy +/- 2 % Active power +/- 0.5 % Apparent power +/- 0.5 % Frequency +/- 0.05 % Power factor +/- 0.5 Current +/- 0.5 % Voltage +/- 0.5 % Apparent energy +/- 0.5 % Reactive power +/- 2 %
Accuracy Class	Class 0.5S active energy conforming to IEC 62053-22
Number Of Outputs	2 relay 2 digital
Information Displayed	Tariff (4)
Communication Port Protocol	Modbus TCP/IP at 10/100 Mbit/s, insulation 2500 V BACnet IP
Communication Port Support	ETHERNET
Data Recording	Alarm logs Time stamping Min/max of instantaneous values Event logs Maintenance logs Data logs
Memory Capacity	256 kB
Connections - Terminals	Voltage circuit: screw terminal block4 Control circuit: screw terminal block2 Current transformer: screw terminal block6 Input/output circuit: screw terminal block6 Relay output: screw terminal block4 Ethernet network: RJ45 connector
Mounting Mode	Flush-mounted
Mounting Support	Framework
Standards	IEC 60529 UL 61010-1 IEC 61557-12:2015 IEC 62053-24 IEC 62053-22:2020 EN 50470-3 EN 50470-1 IEC 62053-23:2020 IEC 62052-11:2020 IEC 62052-31:2015
Product Certifications	CE conforming to IEC 61010-1 CULus conforming to UL 61010-1 MID conforming to EN 50470-1 MID conforming to EN 50470-3
Width	96 mm
Depth	72 mm
Height	96 mm
Net Weight	430 g

Environment

Electromagnetic Compatibility	Limits for harmonic current emissions class A conforming to IEC 61000-3-2 Electrostatic discharge level 4 conforming to IEC 61000-4-2 Conducted RF disturbances level 3 conforming to IEC 61000-4-6 Magnetic field at power frequency level 4 conforming to IEC 61000-4-8 Conducted and radiated emissions class B conforming to EN 55022
Ip Degree Of Protection	IP54 display: conforming to IEC 60529 IP30 rear: conforming to IEC 60529
Relative Humidity	5...95 % at 50 °C non-condensing

Pollution Degree	2
Ambient Air Temperature For Operation	-25...70 °C meter -20...70 °C display -25...-20 °C (with reduced performance) display
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	2000 m CAT III 3000 m CAT II

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.0 cm
Package 1 Width	12.4 cm
Package 1 Length	10.7 cm
Package 1 Weight	550.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.9 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov