

# Product data sheet

Specifications



## Unica - 1 S.O. - 2P+E, shutters, FR - 2 m - ivory

MGU3.039.25

 **Discontinued on:** Feb 21, 2024

 **Discontinued**

### Main

|                             |                            |
|-----------------------------|----------------------------|
| Range                       | Unica                      |
| Product Or Component Type   | Socket-outlet              |
| Aesthetic Name              | Unica (standard aesthetic) |
| Device Presentation         | Mechanism                  |
| Device Mounting             | Flush                      |
| Socket Number               | 1                          |
| Outlet Poles Configuration  | 2P + E                     |
| Outlet Standard             | French                     |
| Outlet Standard Description | Pin earth                  |
| Rated Current               | 16 A                       |

### Complementary

|                                |   |
|--------------------------------|---|
| Device Application             | Power supply  |
| Cover Type                     | With shutter  |
| [Ue] Rated Operational Voltage | 250 V   |
| Network Type                   | AC  |
| Network Frequency              | 50/60 Hz  |
| Number Of Modules              | 2 modules   |
| Fixing Mode                    | Clip-in   |
| Colour Tint                    | Ivory   |
| Connections - Terminals        | Screw terminals   |
| Cable Cross Section            | 0...4 mm <sup>2</sup> - cable stiffness: flexible<br>0...4 mm <sup>2</sup> - cable stiffness: rigid |
| Minimum Load Breaking Capacity | 100 operations 1.25 In and 1.1 Un, cos phi = 0.6  |
| Electrical Durability          | 10000 cycles, cos phi = 0.8   |
| Insulation Resistance          | > 5 MOhm at 500 V   |
| Dielectric Strength            | 2000 V  |
| Material                       | ASA + PC: mechanism cover   |
| Quantity Per Set               | Set of 1 blister  |
| Product Certifications         | 14.10.01/5433<br>FR.ME63.B02375 AC<br>60058890B   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                 |           |
|-----------------|-----------|
| Embedding Depth | 27 mm     |
| Depth           | 37 mm     |
| Width           | 45 mm     |
| Height          | 45 mm     |
| Net Weight      | 0.0362 kg |

## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient Air Temperature For Operation | 15...30 °C  |
| Ambient Air Temperature For Storage   | 0...35 °C   |
| Ik Degree Of Protection               | IK01  |
| Ip Degree Of Protection               | IP20  |
| Environmental Characteristic          | Bleach<br>Petrol<br>Liquid soap<br>Alcohol<br>Window-cleaning fluid<br>UV resistant<br>Acetone<br>Oil |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 4.5 cm  |
| Package 1 Width              | 6.5 cm  |
| Package 1 Length             | 6.5 cm  |
| Package 1 Weight             | 35.0 g  |
| Unit Type Of Package 2       | BB1     |
| Number Of Units In Package 2 | 10      |
| Package 2 Height             | 4.5 cm  |
| Package 2 Width              | 13.5 cm |
| Package 2 Length             | 33.0 cm |
| Package 2 Weight             | 417.5 g |
| Unit Type Of Package 3       | S03     |
| Number Of Units In Package 3 | 120     |
| Package 3 Height             | 30.0 cm |
| Package 3 Width              | 30.0 cm |
| Package 3 Length             | 40.0 cm |
| Package 3 Weight             | 5.37 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |