

# Product data sheet

Specifications



## TeSys LRF - electronic thermal overload relay - 200...330 A - class 10

LR9F7375

⚠ To be discontinued on: Jun 30, 2024

⚠ To be discontinued

### Main

Range	TeSys
Product Name	TeSys LRF
Device Short Name	LR9F
Product Or Component Type	Electronic thermal overload relay
Relay Application	Motor protection
Product Compatibility	LC1F225...LC1F500
Network Type	AC
Thermal Overload Class	Class 10 conforming to IEC 60947-4
Thermal Protection Adjustment Range	200...330 A

### Complementary

Network Frequency	50/60 Hz
Mounting Support	Direct on contactor Plate
Tripping Threshold	1.12 +/- 0.06 In tripping conforming to IEC 60947-4-1
Surge Withstand	4 kV conforming to IEC 61000-4-5
Contacts Type And Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for control circuit
[Ue] Rated Operational Voltage	1000 V AC 50/60 Hz for power circuit conforming to VDE 0110 group C
[Ui] Rated Insulation Voltage	Power circuit: 1000 V AC conforming to IEC 60947-4
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-1
Phase Failure Sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Reset	Manual reset on front relay
Control Type	Dial white full-load current adjustment Test button red Push-button red reset Push-button stop
Local Signalling	Trip indicator
Temperature Compensation	-20...70 °C
Current Consumption	<= 5 mA no-load
Switching Capacity For Alarm	0...150 mA
Maximum Voltage Drop	<2.5 V closed state

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Control circuit: screw clamp terminals 1 cable 0.75...2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable 0.75...2.5 mm <sup>2</sup> - cable stiffness: solid Control circuit: screw clamp terminals 1 cable 0.75...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 1...1.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable 1...2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 1 mm <sup>2</sup> - cable stiffness: solid Power circuit: lugs-ring terminals M10
Tightening Torque	Control circuit: 1.2 N.m on screw clamp terminals Power circuit: 35 N.m on screw clamp terminals
Height	136.8 mm
Width	150 mm
Depth	127.6 mm
Net Weight	2.32 kg

## Environment

Standards	VDE 0660 IEC 60947-4-1 EN 60947-4-1 IEC 60255-17 IEC 60255-8
Product Certifications	UL CSA UKCA
Protective Treatment	TH
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP20 conforming to VDE 0106
Ambient Air Temperature For Operation	-20...55 °C conforming to IEC 60255-8
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	<= 2000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Mechanical Robustness	Shocks: 13 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations 5...300 Hz: 2 GN conforming to IEC 60068-2-6
Dielectric Strength	6 kV 50 Hz conforming to IEC 255-5
Electromagnetic Compatibility	Resistance to electrostatic discharge: 6 kV in indirect mode conforming to IEC 61000-4-2 Resistance to electrostatic discharge: 8 kV in air conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test: 10 V/m conforming to IEC 61000-4-3 Fast transients immunity test: 2 kV conforming to IEC 61000-4-4

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.000 cm
Package 1 Width	20.000 cm
Package 1 Length	19.500 cm
Package 1 Weight	1.882 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	36

Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	79.896 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="#">www.P65Warnings.ca.gov</a>