

Product data sheet

Specifications



Unica - pushbutton switch - 10 A, 250 VAC - 2 m - ivory

MGU3.207.25

 **Discontinued on:** Feb 21, 2024

 **Discontinued**

Main

| | |
|--------------------------------|----------------------------|
| Range | Unica |
| Device Application | Control |
| Product Or Component Type | Shutter control |
| Aesthetic Name | Unica (standard aesthetic) |
| Device Presentation | Mechanism |
| Rated Current | 10 A |
| [Ue] Rated Operational Voltage | 250 V |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Fixing Mode | Clip-in |
| Colour Tint | Ivory |

Complementary

| | |
|--------------------------------|--|
| Device Mounting | Flush |
| Number Of Modules | 2 modules |
| Technology Type | Electromechanical |
| Actuator | Rocker |
| Number Of Rocker | 2 |
| Switch Function | 1-pole 2-way |
| Switch Application | Roller blind |
| Contacts Type And Composition | 1 C/O |
| Mechanical Interlocking | Interlock between up/down |
| [Iu] Rated Interrupted Current | 2.5 A for motor |
| Opening Distance | > 3 mm |
| Marking | UP Down |
| Connections - Terminals | Screwless terminals |
| Cable Cross Section | 2.5 mm² flexible cable 2.5 mm² rigid cable |
| Minimum Load Breaking Capacity | 200 operations 1.25 In and 1.1 Un, cos phi = 0.3 |
| Electrical Durability | 40000 cycles, cos phi = 0.6 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|---|
| Insulation Resistance | > 5 MOhm at 500 V |
| Dielectric Strength | 2000 V |
| Material | ASA + PC: mechanism cover |
| Standards | EN 60669-1 EMC directive LV directive |
| Ambient Air Temperature For Operation | 25...35 °C |
| Ambient Air Temperature For Storage | 0...50 °C |
| Embedding Depth | 22 mm |
| Depth | 34 mm |
| Width | 45 mm |
| Height | 45 mm |
| Net Weight | 0.0382 kg |

Environment

| | |
|------------------------------|---|
| Ik Degree Of Protection | IK01 |
| Ip Degree Of Protection | IP20 |
| Environmental Characteristic | UV resistant Alcohol Acetone Window-cleaning fluid Petrol Liquid soap Bleach Oil |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.500 cm |
| Package 1 Width | 6.500 cm |
| Package 1 Length | 6.500 cm |
| Package 1 Weight | 38.500 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 4.500 cm |
| Package 2 Width | 13.500 cm |
| Package 2 Length | 33.000 cm |
| Package 2 Weight | 455.000 g |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 40 |
| Package 3 Height | 15.000 cm |
| Package 3 Width | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 2.060 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |