

Product data sheet

Specifications



Thermal overload relay, TeSys Deca, 690VAC, 1.6 to 2.5A, 1NO +1NC, class 10A, screw clamp

LRD07

Main

| | |
|-------------------------------------|---|
| Range | TeSys TeSys Deca |
| Product name | TeSys LRD TeSys Deca |
| Product or component type | Differential thermal overload relay |
| Device short name | LRD |
| Relay application | Motor protection |
| Product compatibility | LC1D18 LC1D38 LC1D32 LC1D25 LC1D12 LC1D09 |
| Network type | DC AC |
| Thermal overload class | Class 10A conforming to IEC 60947-4-1 |
| Thermal protection adjustment range | 1.6...2.5 A |
| [Ui] rated insulation voltage | Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL Power circuit: 690 V conforming to IEC 60947-4-1 |

Complementary

| | |
|--|---|
| Network frequency | 0...400 Hz |
| Mounting support | Plate, with specific accessories Rail, with specific accessories Under contactor |
| Tripping threshold | 1.14 +/- 0.06 I _r conforming to IEC 60947-4-1 |
| Auxiliary contact composition | 1 NO + 1 NC |
| [I _{th}] conventional free air thermal current | 5 A for signalling circuit |
| Permissible current | 3 A at 120 V AC-15 for signalling circuit 0.22 A at 125 V DC-13 for signalling circuit |
| [U _e] rated operational voltage | 690 V AC 0...400 Hz for power circuit conforming to IEC 60947-4-1 |
| Associated fuse rating | 4 A gG for signalling circuit 4 A BS for signalling circuit |
| [U _{imp}] rated impulse withstand voltage | 6 kV |

| | |
|----------------------------------|---|
| Phase failure sensitivity | Tripping current 130 % of Ir on two phase, the last one at 0 |
| Control type | Red push-button: stop Blue push-button: reset |
| Temperature compensation | -20...60 °C |
| Connections - terminals | Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² solid without cable end Power circuit: screw clamp terminals 1 cable(s) 1.5...10 mm ² flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 1...4 mm ² flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 1...6 mm ² solid without cable end |
| Tightening torque | Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 1.7 N.m - on screw clamp terminals |
| Height | 66 mm |
| Width | 45 mm |
| Depth | 70 mm |
| Net weight | 0.124 kg |

Environment

| | |
|--|--|
| Climatic withstand | conforming to IACS E10 |
| IP degree of protection | IP20 conforming to IEC 60529 |
| Ambient air temperature for operation | -20...60 °C without derating conforming to IEC 60947-4-1 |
| Ambient air temperature for storage | -60...70 °C |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Vibrations: 6 Gn conforming to IEC 60068-2-6 Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7 |
| Dielectric strength | 1.89 kV at 50 Hz conforming to IEC 60947-1 |
| Standards | EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495 |
| Product certifications | IEC UL CSA CCC EAC BV RINA DNV-GL LROS (Lloyds register of shipping) ATEX INERIS UKCA |

Packing Units

| | |
|-------------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8.8 cm |
| Package 1 Width | 7.7 cm |
| Package 1 Length | 4.9 cm |
| Package 1 Weight | 138 g |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 24 |

| | |
|------------------------------|-----------|
| Package 2 Height | 15 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 3.653 kg |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 384 |
| Package 3 Height | 75 cm |
| Package 3 Width | 60 cm |
| Package 3 Length | 80 cm |
| Package 3 Weight | 72.827 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)