

# Product data sheet

Specifications



## Unica Top/Class - 1 telephone socket - RJ11 - graphite

MGU3.492.12

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

### Main

Range	Unica
Product Or Component Type	Telephone socket
Device Presentation	Mechanism
Colour Tint	Graphite
Telephone Socket Type	RJ11 (4 contacts) - category 3 at 16 Mbit/s

### Complementary

Socket Number	1
Number Of Modules	2 modules
Connections - Terminals	Screw terminals twisted pair
Fixing Mode	Clip-in
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Depth	23 mm
Width	45 mm
Height	45 mm
Embedding Depth	12 mm
Net Weight	0.016 kg
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C

### Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Liquid soap UV resistant Window-cleaning fluid Petrol Alcohol Acetone Bleach Oil

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	4.400 cm
Package 1 Width	6.700 cm
Package 1 Length	6.800 cm
Package 1 Weight	18.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.800 cm
Package 2 Width	13.600 cm
Package 2 Length	33.500 cm
Package 2 Weight	252.000 kg
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1463.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations