


Product data sheet

Specifications



EBExpert MPM-GW, Wireless : EnOcean 868MHz

MPMGWD005045

 **Discontinued on:** Dec 31, 2017

 **Discontinued**

Main

Range	EcoStruxure Building Expert
Product Or Component Type	Gateway
Device Application	Building automation systems
Supply	External supply conforming to CSA
Processor Name	ARM9 32-bit at 400 MHz
Battery Type	Lithium

Complementary

Communication Port Protocol	BACnet , Ethernet ,RJ45 ,10/100 Mbit/s CANbus ,125...500 kbit/s EnOcean , at 868 MHz
[Us] Rated Supply Voltage	24 V AC 50/60 Hz +/- 15 % 24 V DC +/- 10 %
System Requirements	Google Chrome Internet browser Firefox Apple Safari
Power Consumption In W	1.6 W
Power Consumption In Va	5 VA
Communication Gateway	Ethernet/ZigBee
Memory Capacity	64 MB flash
Mounting Mode	Clip-on
Mounting Support	DIN rail
Height	191 mm
Width	116 mm
Depth	45 mm
Enclosure Material	ABS
Standards	ICES-003 CE CSA C22.2

Environment

Ambient Air Temperature For Operation	60 °C
Relative Humidity	90 % non-condensing

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	13.8 cm
Package 1 Length	22.2 cm
Package 1 Weight	0.288 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--------------------------------------------
